

1239190
<https://www.phoenixcontact.com/gb/products/1239190>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 4-position, Socket, straight, M12, coding: T, PCB mounting, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

Commercial data

Item number	1239190
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABQEAD
Product key	ABQAGI
GTIN	4063151459734
Weight per piece (including packing)	7.27 g
Weight per piece (excluding packing)	3.016 g
Country of origin	DE

SACC-CI-M12FST-4CON-L180 TOR SHX - Contact carrier



1239190

<https://www.phoenixcontact.com/gb/products/1239190>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Power
Sensor type	Power
Number of positions	4
Seal present	no
Shielded	yes
Coding	T
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	63 V
Nominal current I_N	12 A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Power
----------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

Connector

Connection 1

SACC-CI-M12FST-4CON-L180 TOR SHX - Contact carrier



1239190

<https://www.phoenixcontact.com/gb/products/1239190>

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	T

Cable/line

Signal type/category	Power
----------------------	-------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked) IP67, when plugged in
Ambient temperature (operation)	-25 °C ... 105 °C -40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Mounting

Mounting type	PCB mounting
---------------	--------------

Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad

SACC-CI-M12FST-4CON-L180 TOR SHX - Contact carrier




1239190

<https://www.phoenixcontact.com/gb/products/1239190>

Drawings

Schematic diagram



Pin assignment of M12 socket, 4-pos., T-coded, socket side view

1239190
<https://www.phoenixcontact.com/gb/products/1239190>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1239190>

 cUL Recognized Approval ID: E468743-20190917				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	63 V	12 A	16	-

 UL Recognized Approval ID: E468743-20190917				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	63 V	12 A	16	-

SACC-CI-M12FST-4CON-L180 TOR SHX - Contact carrier



1239190
<https://www.phoenixcontact.com/gb/products/1239190>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1239190
<https://www.phoenixcontact.com/gb/products/1239190>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk