

KZ 04, KZ 05, KZ 06

Unscreened hook-up wires
High temperature

Applications

Internal wiring in electronic equipment.
Aircrafts and satellites.
Excellent chemical resistance.
In order to increase the operating temperature of the cables up to 250°C, all KZ types can be produced with a nickel plated copper conductor on request.

From 250 to 1000 Volts


Construction

1- CONDUCTOR

Stranded silvered copper wires


2- INSULATION

Extruded polytetrafluorethylene (P.T.F.E.)



Standards

NF C 93-523



-55 °C to +200 °C



Fire retardant
(NF C 32-070/C1)



Flexible



RoHS

KZ - Unscreened hook-up wires, high temperature

NF C 93-523 and Nexans references	Gauge AWG	Cross section mm ²	Construction n x Ø mm	Nom. Ø mm	D.C. resist. at 20°C maxi. Ohms / Km	Overall Ø		Maximum weight Kg / Km	Operating voltage Volts
						mini.	maxi.		
						mm			
KZ 04 - 01	32	0.035	7 x 0.08	0.24	546	0.48	0.58	0.95	250
KZ 04 - 02	30	0.055	7 x 0.10	0.30	349	0.56	0.66	1.3	
KZ 04 - 03	28	0.093	7 x 0.13	0.39	201	0.63	0.73	1.75	
KZ 04 - 04	26	0.14	7 x 0.16	0.48	132	0.74	0.84	2.4	
KZ 04 - 05	24	0.22	7 x 0.20	0.60	86	0.86	0.96	3.4	
KZ 04 - 06	22	0.34	7 x 0.25	0.75	54.4	1.01	1.11	5.0	
KZ 04 - 07	20	0.60	19 x 0.20	1.00	31.3	1.30	1.40	8.25	
KZ 05 - 01	32	0.035	7 x 0.08	0.24	546	0.63	0.84	1.65	600
KZ 05 - 02	30	0.055	7 x 0.10	0.30	349	0.71	0.91	2.1	
KZ 05 - 03	28	0.093	7 x 0.13	0.39	201	0.79	1.00	2.6	
KZ 05 - 04	26	0.14	7 x 0.16	0.48	132	0.89	1.10	3.4	
KZ 05 - 05	24	0.22	7 x 0.20	0.60	86	1.04	1.22	4.5	
KZ 05 - 06	22	0.34	7 x 0.25	0.75	54.4	1.17	1.37	6.2	
KZ 05 - 07	20	0.60	19 x 0.20	1.00	31.3	1.42	1.62	9.5	
KZ 05 - 08	18	0.93	19 x 0.25	1.25	20.5	1.67	1.92	14.1	
KZ 05 - 09	16	1.34	19 x 0.30	1.50	13.9	1.92	2.27	20.0	
KZ 05 - 10	14	1.91	27 x 0.30	1.85	10.0	2.30	2.66	27.0	
KZ 05 - 11	12	3.18	45 x 0.30	2.45	6.0	2.89	3.24	42.5	
KZ 06 - 01	32	0.035	7 x 0.08	0.24	546	0.88	1.09	2.6	1000
KZ 06 - 02	30	0.055	7 x 0.10	0.30	349	0.95	1.16	3.0	
KZ 06 - 03	28	0.093	7 x 0.13	0.39	201	1.04	1.24	3.7	
KZ 06 - 04	26	0.14	7 x 0.16	0.48	132	1.14	1.34	4.6	
KZ 06 - 05	24	0.22	7 x 0.20	0.60	86	1.27	1.47	5.75	
KZ 06 - 06	22	0.34	7 x 0.25	0.75	54.4	1.42	1.63	7.7	
KZ 06 - 07	20	0.60	19 x 0.20	1.00	31.3	1.66	1.86	11.0	
KZ 06 - 08	18	0.93	19 x 0.25	1.25	20.5	1.92	2.17	16.0	
KZ 06 - 09	16	1.34	19 x 0.30	1.50	13.9	2.10	2.41	21.1	
KZ 06 - 10	14	1.91	27 x 0.30	1.85	10.0	2.51	2.92	30.0	
KZ 06 - 11	12	3.18	45 x 0.30	2.45	6.0	3.14	3.55	47.5	