

113A.C - CHROMED ADJUSTABLE WRENCHES | 113A.18C




Norm :

NF ISO 6787, ISO 6787, DIN 3117, ASME B107.100

Description

- Good access to the button = easy setting.
- Non-protruding moving jaw at maximum capacity.
- Pre-adjustment of jaw opening thanks to millimetric gradation.
- Right-hand button rotation.
- Range from 4" to 24".
- Presentation: chromed body and polished head faces.

Information



A [mm]	53
B [mm]	115,0
C1 [mm]	38,5
E [mm]	16,0
E1 [mm]	22,5
E2 [mm]	14,3
E3 [mm]	17,8
E4 [mm]	13,5
L [mm]	456
L1 [mm]	53
[g]	1790