



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Packaging Method: **Bag**
Tensile Strength: **222.411 Newton**
Product Length: **202 mm [8 in]**

Features

Product Type Features

| | |
|------------------|----------------|
| Cable Tie Style | Standard |
| Tensile Strength | 222.411 Newton |

Body Features

| | |
|--------------------------|---------|
| Primary Product Color | Natural |
| Primary Product Material | Nylon |

Dimensions

| | |
|--|-------------------|
| Compatible Cable Bundle Diameter Range | 44.45 mm[1.75 in] |
| Product Length | 202 mm[8 in] |
| Product Width | 4.6 mm[.181 in] |
| Product Thickness | 1.19 mm[.047 in] |

Packaging Features

| | |
|--------------------|-----|
| Packaging Method | Bag |
| Packaging Quantity | 100 |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Out of Scope |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JAN 2025 (247)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #1571982-4
TSS11EGPC04=SLIDE SWITCH SPDT




TE Part #170362-3
MINI UNIVERSAL M-N-L SOCKET




TE Part #2-603227-9
CABLE TIE, NAT, 6" L, 1000/PACK




TE Part #328999
TERMINAL,PIDG R 16-14 3/8




TE Part #100504L
CONT SOC ASSY




TE Part #2160123004
55A0111-22-0



TE Part #7-1879233-5
SMW5 120R 5%



TE Part #2-604771-9
CABLE TIE, NATURAL, 4" (1000)



Documents

Product Drawings

CABLE TIE, 8" L, NATURAL, 100PK

English

Datasheets & Catalog Pages

CABLE TIES

English