


FEATURES

- **Annealed Copper Conductor:** Offers superior electrical conductivity and flexibility.
- **Polyvinyl Chloride Jacket:** Provides excellent insulation and protection against environmental factors.
- **Plain Conductor Type:** Ensures consistent performance and ease of installation.
- **30/0.25 Core Strands:** Enhances flexibility and strength of the cable.
- **Temperature Range -15 °C to 70 °C:** Suitable for use in diverse temperature conditions.
- **Voltage Rating of 500 V:** Supports a wide range of electrical applications.
- **Black Jacket Colour:** Ideal for discreet installations.

RS PRO 1.5 mm² Flexible Cable, 100 m Length

RS Stock No: 606-127



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial settings. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable's PVC jacket provides robust protection, making it suitable for a range of environments.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	Black
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	1.5 mm ²
Cable Length	100 m
Core Strands	30/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	2
Outside Diameter	8.6 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------