



 PRODUCT-DETAILS

AX40-30-01-80

AX40-30-01-80 220-230V50Hz/230-240V60Hz Contactor



General Information

Extended Product Type	AX40-30-01-80
Product ID	1SBL321074R8001
EAN	3471522402806
Catalog Description	AX40-30-01-80 220-230V50Hz/230-240V60Hz Contactor
Long Description	AX32, AX40 contactors are mainly used for controlling 3-phase motors and power circuits up to 690 V AC. These contactors are of the block type design with: – 3 main poles and 1 built-in auxiliary contact – control circuit: AC operated – add-on auxiliary contact blocks for front or side mounting and a wide range of accessories.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Popular Downloads

EPLAN Data	9AAC177929_EPLAN
Data Sheet, Technical	1SBC100187L0203

Information

Instructions and Manuals	9AKK107492A7057
CAD Dimensional Drawing	2CDC001079B0201

Dimensions

Product Net Width	54 mm
Product Net Depth / Length	90 mm
Product Net Height	108.3 mm
Product Net Weight	0.667 kg

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	0
Number of Auxiliary Contacts NC	1
Rated Operational Voltage	Auxiliary Circuit 690 V Main Circuit 690 V
Rated Frequency (f)	Auxiliary Circuit 50 / 60 Hz Main Circuit 50 / 60 Hz
Conventional Free-air Thermal Current (I _{th})	acc. to IEC 60947-4-1, Open Contactors $\Theta = 40^\circ\text{C}$ 65 A acc. to IEC 60947-5-1, $\Theta = 40^\circ\text{C}$ 16 A
Rated Operational Current AC-1 (I _e)	(220 / 240 V) 55 °C 60 A (690 V) 40 °C 60 A (690 V) 70 °C 42 A
Rated Operational Current AC-3 (I _e)	(415 V) 55 °C 40 A (440 V) 55 °C 37 A (500 V) 55 °C 33 A (690 V) 55 °C 25 A (380 / 400 V) 55 °C 40 A (220 / 230 / 240 V) 55 °C 40 A
Rated Operational Current AC-15 (I _e)	(500 V) NC 2 (500 V) 2 A (690 V) 2 A (24 / 127 V) 6 A (220 / 240 V) 4 A (380 / 400 V) 3 A (400 / 440 V) 2 A
Rated Operational Current DC-13 (I _e)	(24 V) 6 A / 144 W (110 V) 0.55 A / 60 W (125 V) 1.1 A / 138 W (220 V) 0.55 A / 121 W (250 V) 0.55 A / 138 W (400 V) 2.8 A / 134 W (500 V) 2 A / 144 W
Rated Operational Power AC-3 (P _e)	(415 V) 18.5 kW (440 V) 22 kW (500 V) 22 kW (690 V) 22 kW (380 / 400 V) 18.5 kW (220 / 230 / 240 V) 11 kW
Rated Short-time Withstand Current Low Voltage (I _{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 400 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 65 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 150 A

	at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 600 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 225 A for 0.1 s 140 A for 1 s 100 A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for I _e > 100 A) at 440 V 820 A cos phi=0.45 (cos phi=0.35 for I _e > 100 A) at 690 V 340 A
Rated Insulation Voltage (U _i)	acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V
Rated Impulse Withstand Voltage (U _{imp})	Auxiliary Circuit 6 kV
Maximum Electrical Switching Frequency	(AC-1) 600 cycles per hour (AC-15) 1200 cycles per hour (AC-3) 1200 cycles per hour (DC-13) 900 cycles per hour
Maximum Mechanical Switching Frequency	3600 cycles per hour
Rated Control Circuit Voltage (U _c)	50 Hz 220 ... 230 V 60 Hz 230 ... 240 V
Power Loss	at Rated Operating Conditions AC-1 per Pole 3 W at Rated Operating Conditions AC-3 per Pole 1.3 W
Operate Time	Between Coil De-energization and NC Contact Closing 7 ... 14 ms Between Coil De-energization and NO Contact Opening 4 ... 11 ms Between Coil Energization and NC Contact Opening 6 ... 18 ms Between Coil Energization and NO Contact Closing 8 ... 21 ms
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Tightening Torque	Auxiliary Circuit 1 N·m Control Circuit 1 N·m Main Circuit 2.3 N·m
Terminal Type	Screw Terminals
Product Name	Block Contactor

Technical UL/CSA

General Use Rating UL/CSA	(600 V AC) 60 A
Horsepower Rating UL/CSA	(120 V AC) Single Phase 3 hp (200 ... 208 V AC) Three Phase 10 hp (220 ... 240 V AC) Three Phase 15 hp (240 V AC) Single Phase 7.5 hp (440 ... 480 V AC) Three Phase 30 hp (550 ... 600 V AC) Three Phase 40 hp
Tightening Torque UL/CSA	Auxiliary Circuit 9 in·lb Control Circuit 9 in·lb Main Circuit 20 in·lb
Full Load Amps Motor Use	(120 V AC) Single Phase 34 A (200 ... 208 V AC) Three Phase 32.2 A (220 ... 240 V AC) Three Phase 42 A (240 V AC) Single Phase 40 A (440 ... 480 V AC) Three Phase 40 A (550 ... 600 V AC) Three Phase 41 A

Environmental

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay -25 ... 55 °C Close to Contactor without Thermal O/L Relay -40 ... 70 °C Close to Contactor for Storage -60 ... +80 °C Near Contactor for Operation in Free Air -40 ... 70 °C
Climatic Withstand	according to IEC 60068-2-30 and 60068-2-11 - UTE C 63-100 Specification II
Maximum Operating	Without Derating 3000 m

Altitude Permissible

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS Declaration	2CMT2021-006277
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	86e14de5-1272-47d3-a4e4-745525083f43 Bulgaria
Simplified SCIP	01184b37-26cf-4ccd-a40e-21ee1f999fdb Germany 14999228-11e9-47e5-b3d5-e9e1ec2e25f3 Germany 3094a197-28cb-4554-a22b-605b6038d806 Hungary 3741b36c-a743-4d2b-8208-15a55f05eb43 Estonia 37721f49-a8de-4d3a-bc37-667bf8dff0d3 Poland 43addf7e-6d9d-43e8-a9e8-29347fe351ab Czech Republic 47366213-0938-4915-9ef8-4bb4cf7541da Netherlands 4f338bbe-fc39-49ab-9a4d-edd7444f967a Poland 575a0e50-88cd-48df-835d-f3cbb137d86d Germany 70743583-e2cd-4cd8-bb11-91a4252fd4bc Germany 7920640a-f521-479b-b515-2341b365c0b8 Germany 7ec270d4-73b4-4668-9452-a580f4f77c67 France 8200344d-0b64-4253-a049-5e4bd48c04a2 Belgium 82a06ece-4bfd-4193-a6d1-8ccaa134ca19 Sweden 95c811ae-b70e-4d4f-9f05-a5975c4e797a France 9a926ad5-286e-41be-b9b3-39e9a1c74cde Spain a0c7c954-6eba-493e-9cda-329e7b08aac9 Greece b01f5b9f-c8d4-4ba5-be5a-17dd68f8f4a9 Belgium cb79da2c-9012-43f1-bff6-ec0aee72b5a8 Italy d14f4ce6-3547-4e11-aa0d-1eac75140441 Hungary d3bc14a1-f8ee-45ce-bd4f-4b00c21c408c Poland d4117384-cd61-493c-8a09-ac9717acbd2e Denmark d461fe48-9704-47a8-9e5b-5585dff8e934 Norway da63b6cb-9cdc-4342-b861-b76bf47ee529 Finland ec31e6c2-3521-48a0-93e4-136529fa28b9 Sweden fa44e3ff-bdaf-41c5-916c-23832c3050e1 Croatia fc8bb500-6f0c-4e44-850c-913fa4c950b3 Portugal
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

ABB EcoSolutions

Environmental Product Declaration - EPD	No Declaration Needed
---	-----------------------

Certificates and Declarations

CB Certificate	9AKK107492A7073
CCC Certificate	9AKK107492A7090
CCS Certificate	GZ23PTB00147
CQC Certificate	CQC2013010304647116
Declaration of Conformity - CCC	2020980304001065
Declaration of Conformity - CE	1SBD250011U1000
UL Certificate	UL_20140702-E312527-10-6

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	65 mm
Package Level 1 Depth / Length	101 mm
Package Level 1 Height	115 mm
Package Level 1 Gross Weight	0.71 kg
Package Level 1 EAN	3471522402806

External Classifications and Standards

Object Classification Code	Q
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 8	EC000066 - Power contactor, AC switching
ETIM 9	EC000066 - Power contactor, AC switching
eClass	V11.0 : 27371003
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4755 >> Contactors
E-Number (Finland)	3707346

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
1SBN010015R1001	CE5-01D0.1 Auxiliary Contact Block	CE5-01D0.1	1	piece
1SBN010015R1010	CE5-10D0.1 Auxiliary Contact Block	CE5-10D0.1	1	piece
1SBN010016R1001	CE5-01W0.1 Auxiliary Contact Block	CE5-01W0.1	1	piece
1SBN010016R1010	CE5-10W0.1 Auxiliary Contact Block	CE5-10W0.1	1	piece
1SBN010017R1001	CE5-01D2 Auxiliary Contact Block	CE5-01D2	1	piece
1SBN010017R1010	CE5-10D2 Auxiliary Contact Block	CE5-10D2	1	piece
1SBN010018R1001	CE5-01W2 Auxiliary Contact Block	CE5-01W2	1	piece
1SBN010018R1010	CE5-10W2 Auxiliary Contact Block	CE5-10W2	1	piece

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors → AX Contactors → AX40

