

## Features

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.

## RS PRO Oilite® Flanged Bearing

RS Stock No.: 0528048




RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

RS PRO is offering range of Oilite® plain bearings - self-lubricating bearings that are made from metal alloys with pores that channel lubricants between the bearing itself and the shaft.

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- Lubricant : Shell Tellus S2 MX68
- Temperature range of -15°C to +75°C.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.
- All dimensions and tolerances of our metric ranges conform to ISO 2795:1991
- Wide range of metric and imperial sizes
- Wide range of different types: Plain, Flanged

\* Below dimensions in mm



## Specifications

### Details

Inner Diameter	10	Outer Diameter	16	Length	12
Tolerance Range	UK Standard	Flange Thickness	3	Flange Diameter	22

### Material Specification

Structure	Oil impregnated sintered bronze*		
Max PV (N/mm <sup>2</sup> x m/s)	1.8	Max Static load (N/mm <sup>2</sup> )	50
Max Dynamic load (N/mm <sup>2</sup> )	14	Max Sliding speed (m/s)	5
Operating temperature (°C)	-60 to 200*	Density (g/cm <sup>3</sup> )	6.6
*dependant on lubrication			
Radial crushing strength (K Min M/mm <sup>2</sup> )	160		

### Tolerances & Fittings (Metric)

	Min	Max	Tolerance
Inside Diameter	10.005	10.024	G7
Outside Diameter	16.028	16.046	s7
Overall Length	11.865	12.135	js13
Flange Thickness Tolerance	2.930	3.070	js13
Flange Diameter Tolerance	21.835	22.165	js13
Recommended Housing Size	16.000	16.018	H7
Shaft Diameter	9.972	9.987	f7
Fitting Pin Size	10.006	10.012	m5
Concentricity Max	0.043	0.043	IT9
Inside Diameter When Fitted	10.000	10.015	H7