

Eaton 087792

Catalog Number: 087792

Eaton Moeller® series MCS Pressure switch, 2W gold-plated, 7bar



General specifications

Product Name	Catalog Number
Eaton Moeller® series MCS Pressure switch	087792

EAN
4015080877929

Product Length/Depth	Product Height
111 mm	66 mm

Product Width	Product Weight
96 mm	0.383 kg

Certifications

CSA Class No.: 3211-06
CSA-CC22.2 No. 14
IEC/EN 60947-5-1
CSA
CSA File No.: 012528

Catalog Notes

Note on use:
This product
complies with
Low-Voltage
Directive
2014/35/EC and
EMC Directive
2014/30/EC and
meets the
requirements in
EN 60947-5-1.
This product
does not meet
the rail
industry's
standard
requirements.
Accordingly, the
user must
review it

Product specifications

Suitable as

2-point controller

Guard

Features

Variable switching differential

Thread size

1/2 inch

1/4 inch

Electric connection type

Screw connection

Operating frequency

1500 Operations/h

Pollution degree

3

Actuator diameter

0 mm

Adjustable current range - max

0 A

Adjustable current range - min

0 A

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Bursting pressure

90 bar

End setting - max

0 hPa

End setting - min

0 hPa

End value measuring range pressure

0 Pa

Engaging pressure - max

4.2 bar

Engaging pressure - min

0 bar

Resources

Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Characteristic curve

[eaton-pressure-switches-diagram-mcs-pressure-switch-characteristic-curve.eps](#)

Declarations of conformity

[DA-DC-00004159.pdf](#)

[DA-DC-00004137.pdf](#)

Drawings

[eaton-pressure-switches-switch-mcs-pressure-switch-dimensions.eps](#)

[eaton-pressure-switches-switch-mcs-pressure-switch-dimensions-003.eps](#)

[eaton-pressure-switches-mcs-pressure-switch-dimensions.eps](#)

Installation instructions

[IL05212001Z](#)

mCAD model

[mcs_n.dwg](#)

[mcs_n.stp](#)

Initial setting - max

0 hPa

Initial setting - min

0 hPa

Initial value measuring range pressure

0 Pa

Medium temperature - max

80 °C

Medium temperature - min

25 °C

Number of auxiliary contacts (change-over contacts)

2

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Degree of protection

IP65

NEMA Other

Rated impulse withstand voltage (Uimp)

1500 V AC

Environmental conditions

Compliant to 2014/35/EC, 2014/30/EC and EN 60947-5-1.

Accordingly, the user must review it separately for the specific application at hand.

Connection

Inner thread gas cylindrical (BSPP)

Mounting position

Vertical and 90° in all directions

Connection type

Tunnel terminal

Overvoltage category

III

Lifespan, electrical

1,000,000 Operations

Number of contacts (normally closed) as main contact

0

Number of main contacts (normally open contact)

0

Operating pressure - max

7000 hPa

Pressure differential

0 bar

Rated frequency - max

50 Hz

Rated insulation voltage (Ui)

125 V

Rated operational current (Ie) at AC-1, 380 V, 400 V, 415 V

0 A

Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V

0 A

Rated operational power at AC-3, 380/400 V, 50 Hz

0 kW

Rated operational voltage (Ue) at AC - max

0 V

Rated operational voltage (Ue) at AC - min

0 V

Rated operational voltage (Ue) at DC - max

110 V

Rated operational voltage (Ue) at DC - min

0 V

Switch off pressure - max

4.5 bar

Switch off pressure - min

0 bar

Switching capacity at AC-3, 240 V

0 kA

Test pressure

32 bar

Product category

Pressure switches

Screw size

M2.6, Terminal screw

Rated operational current (Ie)

2 A at AC-15, 230 V, 50/60Hz

0.25 A at DC-13, 110 V

1 A at DC-13, 24 V

Shock resistance

10 g, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms

Short-circuit protection rating

Max. 2 A gG/gL, Fuse, Contacts

Terminal capacity (solid)

1 x (0.75 - 2.5) mm²

2 x (0.75 - 1.5) mm²

Terminal capacity (flexible with ferrule)

1 x (0.5 - 1.5) mm², ferrules to DIN 46228

Tightening torque

0.4 Nm, Screw terminals

Vibration resistance

36 Hz, Amplitude 1 mm, (IEC/EN 60068-2-6)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia