

Printed-circuit board connector - PC 6/ 3-G1-7,62 BK - 1717017

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Header, nominal current: 41 A, rated voltage (III/2): 630 V, number of positions: 3, pitch: 7.62 mm, color: black, contact surface: Tin

The figure shows the 4-position version

Why buy this product



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	25 STK
GTIN	 4 055626 514949
GTIN	4055626514949
Custom tariff number	85366930
Country of origin	China

Technical data

Item properties

Brief article description	Printed-circuit board connector
Range of articles	PC 6/..-G1
Pitch	7.62 mm
Type of contact	Male connector
Plug-in system	POWER COMBICON 6
Number of positions	3
Mounting type	Wave soldering

Printed-circuit board connector - PC 6/ 3-G1-7,62 BK - 1717017

Technical data

Item properties

Number of levels	1
------------------	---

Electrical parameters

Rated current	41 A
Rated insulation voltage (III/2)	630 V
Rated surge voltage (III/2)	6 kV

Material data - contact

Contact material	Cu alloy
Surface characteristics	hot-dip tin-plated
Metal surface contact area (top layer)	Tin Sn
Metal surface soldering area (top layer)	Tin Sn

Material data - housing

Housing color	black (9005)
---------------	--------------

Dimensions for the product

Length [l]	28.2 mm
Width [w]	23.26 mm
Pitch	7.62 mm
Height (without solder pin)	13.5 mm
Solder pin [P]	2.6 mm
Pin dimensions	0.8 x 1 mm
Dimension a	15.24 mm

Packaging information

Type of packaging	packed in cardboard
Pieces per package	25
Denomination packing units	Pcs.

Air clearances and creepage distances

Insulating material group	I
Voltage	630 V
Rated insulation voltage (III/3)	630 V
Rated insulation voltage (III/2)	630 V
Rated insulation voltage (II/2)	1000 V
Rated surge voltage (III/3)	6 kV
Rated surge voltage (III/2)	6 kV
Rated surge voltage (II/2)	6 kV

Printed-circuit board connector - PC 6/ 3-G1-7,62 BK - 1717017

Classifications

eCl@ss

eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

Accessories

Accessories

Coding element

Coding profile - CP-PC RD - 1701967



Coding profile, for plugging into the coding ribs of the plug at a later date, insulating material, color: Red

Additional products

Printed-circuit board connector - LPC 6/ 3-ST-7,62 - 1716922



Plug component, nominal current: 41 A, rated voltage (III/2): 1000 V, number of positions: 3, pitch: 7.62 mm, connection method: Push-in spring connection, color: green, contact surface: Tin