


KMK 4

Order No.: 1005305



Plastic cable marker, without tie, labeling with insert strips ESL..., EST... or large format ES/KMK 3-GB, attachment with cable binder PKB, lettering field size: 40 x 17 mm

Commercial data	
EAN	 4 017918 012496
Pack	50
Customs tariff	39269098
Country of Origin	DE
Catalog page information	Page 177 (CL2-2011)

Product notes

WEEE/RoHS-compliant since:
01/01/2003



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
General	
Height	17 mm
Width (a)	40 mm
Color	transparent
Ambient temperature (operation)	-40 °C ... 80 °C

Components	free from silicone and halogen
Material	Polyethylene

Accessories

Item	Designation	Description
------	-------------	-------------

General

0824403	ESL 40X17 CUS	Labels, color: white, can be labeled according to customer requirements
---------	---------------	---

Marking

0817293	EMT (40X17)R	Insert strips, can be labeled using a thermal transfer printer, can be labeled using THERMOMARK-RIBBON 110 ink ribbon (5145384), lettering field size: 40 mm x 17 mm, roll = 2300 labels, color: white
0824385	EMT (40X17)R CUS	Insert strips, marked according to customer instructions, lettering field size: 40 mm x 17 mm, 1 roll = 2300 labels, color white
0808095	ESL 40X17	Insert strip for laser printer, perforated, for terminal strip markers UBE/D or UBE, lettering field size: 40 x 17 mm, labeling with laser printer, M-PEN or CMS system, 56-section
0829437	US-EMP (40X17)	UniSheet labels to be snapped into the marker carrier, can be labeled with THERMOMARK CARD, 16-section, color: white