



Sensors > Pressure Sensors > Media Isolated Pressure Sensors > 19MM MV OUTPUT PRESSURE SENSOR



Pressure Sensor Type: **mV Output Pressure Sensors**
Pressure Type: **Gauge**
Output Signal Type: **100mV**
Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**
Sensor Package: **O-Ring Mount**

[All 19MM MV Output Pressure Sensor \(38\)](#)

Features

Product Type Features

Pressure Sensor Type	mV Output Pressure Sensors
Pressure Type	Gauge
Sensor Package	O-Ring Mount

Configuration Features

Electrical Connection	Ribbon Cable
-----------------------	--------------

Electrical Characteristics

Supply Current	1.5 mA
----------------	--------

Dimensions

Product Diameter	18.97 mm[.746 in]
Product Height	13.8 mm[.54 in]

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Proof Pressure Range	3X
Output Signal Type	100mV



Other

Non-Linearity ±	.1 %
Sensor Options	Vent Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Tetraglyme (2% in Component Part) Methanone, (diphenylphosphinyl)(2,4,6-trimethylphenyl)- (1% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-MIPS0002
19MM MV OUTPUT PRESSURE
SENSOR

Also in the Series

MEAS 154



Media Isolated Pressure Sensors(74)

Customers Also Bought

 TE Part #20007013-00 4610-002-120-D	 TE Part #10217784-00 ABD,AD-101, COMPACT ASSY, 4MM	 TE Part #20009605-05 FX292X-100A-0025-L	 TE Part #86-500G-U NISO,LP,GAGE,LEADS
 TE Part #86-100G-U NISO,LP,GAGE,LEADS	 TE Part #86-300G-U NISO,LP,GAGE,LEADS	 TE Part #20031528-00 PT1000 TEMPERATURE SENSOR, CLA, 250MM	 TE Part #20031528-01 PT1000 TEMPERATURE SENSOR, CLA, 900MM
 TE Part #M3031-000005-01KPG PRESS XDCR M3031-000005-01KPG	 TE Part #86A3R-000000-050PG NISO,LP,GAGE,R-CABLE,MDL 86A		



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_154N-030G-RT_F1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_154N-030G-RT_F1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_154N-030G-RT_F1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

154NC

English