



## Main

Range	New Unica
Product or component type	Socket-outlet
Device presentation	Mechanism
Device mounting	Flush
Socket number	1
Outlet poles configuration	2P + E
Outlet standard deviation	American
Outlet standard description	Centred earth
Rated current	15 A

## Complementary






Device application	Power supply
Cover type	With shutter
[Ue] rated operational voltage	127 V
Network type	AC
Network frequency	50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)
Connections - terminals	Screw terminals
Cable cross section	0...4 Mm <sup>2</sup> cable(s), 2 - cable stiffness: flexible 0...4 mm <sup>2</sup> - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	PC: mechanism cover PC (polycarbonate) GF10 FR: casing
Surface finish	Painted
Quantity per set	Set of 1 flow-pack
Standards	IEC 60884-1
Embedding depth	24 mm
Depth	33.5 mm
Width	22.5 mm
Height	45 mm
Net weight	0.0354 kg

Surface treatment	Painted
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK01
IP degree of protection	IP21D
Environmental characteristic	Liquid soap Window-cleaning fluid Oil Acetone Alcohol Petrol Bleach UV resistant

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations