

Pole Hedge Trimmer LXT®

DUN600L

18V • 600 mm

Hedge trimmer with loop handle and brushless motor with long handle is very suitable for cutting tall and long hedges. The new three-blade cutting teeth are designed to cut easily and reduce cutting friction.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	1000 / 1800 / 2000 min ⁻¹
Strokes per Minute (SPM)	2000 / 3600 / 4400 min ⁻¹
Length Of Blade	600 mm
Max blade opening	23,5 mm
Continuous Use 18V / 6.0 Ah Battery	55 / 80 / 180 min
Sound Power Level (L _{WA})	93 dB(A)
Sound Pressure Level (L _{pA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	3,8 / 2,7 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²

User benefits

- Lightweight for reduced operator fatigue
- Reverse rotation system frees the blade when it is jammed by thick branches
- Constant speed control maintains constant speed under load
- Electric brake for maximum productivity and increased operator safety
- Non-angle adjustable hedge trimmer head
- Soft grip handle provides increased comfort on the job
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

■ Optional AC

458414-1
Blade Cover, 600 mm



783202-0
Hex Wrench 4Mm



■ Other

User manual

Parts drawing