



Chemical protection


# ULTRANE0 339

Prolonged contact (or immersion) | continuous wear

## Comfort and high-level chemical protection



CHEMICAL PROTECTION  
**TYPE A**



### SPECIFIC ADVANTAGES



#### Thermal protection

- Thermal insulation from the cotton-knit lining for handling hot liquids



#### Durability

- Excellent mechanical resistance and longer service life, due to the textile support and the thickness of the glove



#### Productivity

- Pebbled embossing, for better grip on wet and slippery objects



#### Skin protection

- Superior chemical resistance against acids and alkalis, such as concentrated hydrofluoric acid, oils, and greases, due to its 100% neoprene multi-layer construction



#### Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

### INDUSTRIES

- Mechanical industry
- Chemical industry

### APPLICATIONS

- Surface treatment of metals (acids)
- Handling and transporting drums of chemical products
- Handling on alkylation units
- Hot, petrochemical product sampling
- Resin-working
- Site pollution control



Chemical protection

# ULTRANEО 339

Prolonged contact (or immersion) | continuous wear

## LEGENDS

|                         |                                                |
|-------------------------|------------------------------------------------|
| EN388                   | MECHANICAL HAZARDS                             |
|                         | PERFORMANCE LEVELS (X = NOT TESTED)            |
| 3 1 2 1 X               |                                                |
| 0-4 0-5 0-4 0-4 A-F P   |                                                |
|                         | Impact protection (optional)                   |
|                         | Cut resistance according to ISO 13997          |
|                         | Puncture resistance                            |
|                         | Tear resistance                                |
|                         | Blade cut resistance                           |
|                         | Abrasion resistance                            |
| EN407                   | THERMAL RISKS (HEAT AND FIRE)                  |
|                         | PERFORMANCE LEVELS (X = NOT TESTED)            |
| X 1 X X X X             |                                                |
| 0-4 0-4 0-4 0-4 0-4 0-4 |                                                |
|                         | Resistance to large quantities of molten metal |
|                         | Small splashes of molten metal                 |
|                         | Radiant heat resistant                         |
|                         | Convective heat resistance                     |
|                         | Contact heat resistance                        |
|                         | Limited flame spread                           |
| EN ISO 374-1            | CHEMICAL RISKS                                 |
|                         | A: Methanol                                    |
| TYPE A                  | B: Acetone                                     |
|                         | C: Acetonitrile                                |
|                         | J: n-Heptane                                   |
|                         | L: Sulphuric acid 96%                          |
|                         | M: Nitric acid 65%                             |
|                         | N: Acetic acid 99%                             |
|                         | S: Hydrofluoric acid 40%                       |

## PRODUCT DETAILS

|                                                                                         |                 |
|-----------------------------------------------------------------------------------------|-----------------|
| Interior finish                                                                         | Textile support |
| Exterior finish                                                                         | Pebbled         |
| Material                                                                                | Polychloroprene |
| Cuff characteristic                                                                     | Feston Cuff     |
| Colour.s                                                                                | Black           |
| Length (cm)                                                                             | 36              |
| Thickness (mm)                                                                          | 1.35            |
| European sizes                                                                          | 9 10            |
| Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)  | 2.9E+11 Ω       |
| Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity) | 1.2E+11 Ω       |

## LOGISTIC DETAILS

|           |                              |
|-----------|------------------------------|
| Packaging | 1 pair/bag<br>6 pairs/carton |
|-----------|------------------------------|

## LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/12/18/2912
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France