

## CP0175 v3.8 RS 850-990

**SAFETY DATA SHEET**  
GENERAL PURPOSE ADHESIVE

Page: 1

Compilation date: 20/09/2019

Revision No: 11

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** GENERAL PURPOSE ADHESIVE

**Product code:** RS850-990

UFI No. 9RM0-90DN-K00S-J9A1

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** PC1: Adhesives, sealants.

**1.3. Details of the supplier of the safety data sheet**

**Company name:** RS Components Ltd

Birchington Road

Corby

Northamptonshire

NN17 9RS

England

**Tel:** +44 (0) 845 850 9900

**Email:** [RCustomerServicesUK@rs-components.com](mailto:RCustomerServicesUK@rs-components.com)

RS Components Ltd

Glenview Industrial Estate

Herberton Road

Rialto

Dublin 12

+353 (0) 1 415 3100

[enquiries.ie@rs-components.com](mailto:enquiries.ie@rs-components.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 1865 407333 (24hr) +44 1235 239670 (24hr)

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066

**Most important adverse effects:** Repeated exposure may cause skin dryness or cracking. Highly flammable liquid and vapour. Causes serious eye irritation. May cause drowsiness or dizziness.

**2.2. Label elements**

**Label elements:**

**Hazard statements:** EUH066: Repeated exposure may cause skin dryness or cracking.

H225: Highly flammable liquid and vapour.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

**Hazard pictograms:** GHS02: Flame

GHS07: Exclamation mark



**Signal words:** Danger

[cont...]

# SAFETY DATA SHEET

## GENERAL PURPOSE ADHESIVE

Page: 2

**Precautionary statements:** P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P261: Avoid breathing dust/fumes/gas/mist/vapours/spray.  
P271: Use only outdoors or in a well-ventilated area.  
P243: Take action to prevent static discharges.  
P280: Wear protective gloves/protective clothing/eye protection/face protection.  
P303+P361+P353: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water .  
P304+P340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P312: Call a POISON CENTRE or doctor if you feel unwell.  
P370+P378: In case of fire: Use media other than water to extinguish.

**Haz. ingredients (label):** ACETONE; ETHYL METHYL KETONE

### 2.3. Other hazards

**Other hazards:** In use, may form flammable / explosive vapour-air mixture.

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

ACETONE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
200-662-2	67-64-1	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	30-50%

ETHYL METHYL KETONE

201-159-0	78-93-3	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	30-50%
-----------	---------	---	--	--------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Transfer to hospital for specialist examination.

**Ingestion:** Consult a doctor. If conscious, give half a litre of water to drink immediately. Do not induce vomiting. Transfer to hospital as soon as possible.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

[cont...]

# SAFETY DATA SHEET

## GENERAL PURPOSE ADHESIVE

Page: 3

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be vomiting. Nausea and stomach pain may occur.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes. Vapour may travel considerable distance to source of ignition and flash back. Highly flammable. Forms explosive air-vapour mixture.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Refer to section 13 of SDS for suitable method of disposal.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

[cont...]

**SAFETY DATA SHEET**  
GENERAL PURPOSE ADHESIVE

Page: 4

**Section 7: Handling and storage**

**7.1. Precautions for safe handling**

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.  
Do not handle in a confined space. Smoking is forbidden.

**7.2. Conditions for safe storage, including any incompatibilities**

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Ensure lighting and electrical equipment are not a source of ignition.

**Suitable packaging:** Must only be kept in original packaging.

**7.3. Specific end use(s)**

**Specific end use(s):** No data available.

**Section 8: Exposure controls/personal protection**

**8.1. Control parameters**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	600mg/m <sup>3</sup>	900mg/m <sup>3</sup>	-	-

**Hazardous ingredients:**

**ACETONE**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1210 mg/m <sup>3</sup>	3620 mg/m <sup>3</sup>	-	-

**ETHYL METHYL KETONE**

UK	600 mg/m <sup>3</sup>	899 mg/m <sup>3</sup>	-	-
----	-----------------------	-----------------------	---	---

**DNEL/PNEC Values**

**DNEL / PNEC** No data available.

**8.2. Exposure controls**

**Engineering measures:** Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency. Gas/vapour filter, type A: organic vapours (EN141). Compressed airline breathing apparatus (EN139).

**Hand protection:** Protective gloves. Viton gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

[cont...]

**SAFETY DATA SHEET**  
GENERAL PURPOSE ADHESIVE

Page: 5

**Section 9: Physical and chemical properties**

**9.1. Information on basic physical and chemical properties**

**State:** Liquid  
**Colour:** Colourless  
**Odour:** Perceptible odour  
**Evaporation rate:** Fast  
**Solubility in water:** Insoluble  
**Viscosity:** Non-viscous  
**Boiling point/range°C:** 56  
**Flammability limits %: lower:** 0.6  
**upper:** 13  
**Flash point°C:** -19  
**Autoflammability°C:** 515  
**Relative density:** 0.86

**9.2. Other information**

**Other information:** No data available.

**Section 10: Stability and reactivity**

**10.1. Reactivity**

**Reactivity:** Stable under recommended transport or storage conditions.

**10.2. Chemical stability**

**Chemical stability:** Stable under normal conditions.

**10.3. Possibility of hazardous reactions**

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

**10.4. Conditions to avoid**

**Conditions to avoid:** Sources of ignition. Flames.

**10.5. Incompatible materials**

**Materials to avoid:** Oxidising agents.

**10.6. Hazardous decomposition products**

**Haz. decomp. products:** In combustion emits toxic fumes.

**Section 11: Toxicological information**

**11.1. Information on toxicological effects**

**Toxicity values:**

Route	Species	Test	Value	Units
-------	---------	------	-------	-------

[cont...]

**SAFETY DATA SHEET**  
GENERAL PURPOSE ADHESIVE

Page: 6

ORL	RAT	LD50	>5000	mg/kg
-----	-----	------	-------	-------

**Hazardous ingredients:**

**ACETONE**

IVN	RAT	LD50	5500	mg/kg
ORL	MUS	LD50	3000	mg/kg
ORL	RAT	LD50	5800	mg/kg

**ETHYL METHYL KETONE**

IPR	-	-	-	-
-----	---	---	---	---

**Relevant hazards for product:**

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

**Symptoms / routes of exposure**

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be vomiting. Nausea and stomach pain may occur.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

**Section 12: Ecological information**

**12.1. Toxicity**

**Hazardous ingredients:**

**ACETONE**

BLUEGILL ( <i>Lepomis macrochirus</i> )	LC50	8300	mg/l
---	------	------	------

**12.2. Persistence and degradability**

**Persistence and degradability:** Biodegradable in part only.

**12.3. Bioaccumulative potential**

**Bioaccumulative potential:** No data available.

**12.4. Mobility in soil**

**Mobility:** Volatile.

**12.5. Results of PBT and vPvB assessment**

**PBT identification:** This product is not identified as a PBT/vPvB substance.

[cont...]

**SAFETY DATA SHEET**  
GENERAL PURPOSE ADHESIVE

Page: 7

**12.6. Other adverse effects**

**Section 13: Disposal considerations**

**13.1. Waste treatment methods**

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Disposal of packaging:** Arrange for collection by specialised disposal company.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

**Section 14: Transport information**

**14.1. UN number**

**UN number:** UN1133

**14.2. UN proper shipping name**

**Shipping name:** ADHESIVES  
(ACETONE; ETHYL METHYL KETONE)

**14.3. Transport hazard class(es)**

**Transport class:** 3

**14.4. Packing group**

**Packing group:** II

**14.5. Environmental hazards**

**Environmentally hazardous:** No

**Marine pollutant:** No

**14.6. Special precautions for user**

**Special precautions:** No special precautions.

**Tunnel code:** D/E

**Transport category:** 2

**Section 15: Regulatory information**

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

**15.2. Chemical Safety Assessment**

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

**Section 16: Other information**

**Other information**

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

[cont...]

**SAFETY DATA SHEET**  
GENERAL PURPOSE ADHESIVE

**Page: 8**

**Phrases used in s.2 and s.3:** EUH066: Repeated exposure may cause skin dryness or cracking.

H225: Highly flammable liquid and vapour.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.