





STANDARD VERSION




HIGH VOLTAGE VERSION




INSULATING ADHESIVE TAPE
ON BOTH SIDES

SUITABLE FOR
HIGH VOLTAGE INSERTS



SCALE 2:3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex		
mm		1:1								
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 666475 DRWN: CRAODOREMS 2021/05/20 CHK'D: DMERONI 2021/06/07 APPR: MBIZZOZERO 2021/06/09				24B HOOD 4 PEGS HIGH CONSTRUCTION TOP ENTRY SERIES		
ANGULAR TOL ± 1.0 °										
4 PLACES		±								
3 PLACES		±		INITIAL REVISION: DRWN: CRAODOREMS 2021/05/20 APPR: MBIZZOZERO 2021/06/09				PRODUCT CUSTOMER DRAWING		
2 PLACES		± 0.1								
1 PLACE		± 0.2								
0 PLACES		± 0.3		DOCUMENT NUMBER 936013704				DOC TYPE	DOC PART	REVISION
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								FIRST ANGLE PROJECTION 	DRAWING A3-SIZE	SERIES 93601

	10	9	8	7	6	5	4	3	2	1																																																																																				
F											F																																																																																			
E											E																																																																																			
D											D																																																																																			
C											C																																																																																			
B											B																																																																																			
A											A																																																																																			
<table><tr><td colspan="2">TABLE 1</td><td colspan="3">PRODUCTS TABLE</td></tr><tr><td>MATERIAL No.</td><td>Eng.No.</td><td>TYPE</td><td>D1</td></tr><tr><td>0936013704</td><td>7824.6489.5</td><td rowspan="4">STD</td><td>M32x1.5</td></tr><tr><td>0936013714</td><td>7824.6490.5</td><td>M40x1.5</td></tr><tr><td>0936013670</td><td>7824.6475.5</td><td>Pg21</td></tr><tr><td>0936013680</td><td>7824.6476.5</td><td>Pg29</td></tr><tr><td>0936013706</td><td>7824.6489.7</td><td rowspan="4">HV</td><td>M32x1.5</td></tr><tr><td>0936013716</td><td>7824.6490.7</td><td>M40x1.5</td></tr><tr><td>0936013672</td><td>7824.6475.7</td><td>Pg21</td></tr><tr><td>0936013683</td><td>7824.6476.7</td><td>Pg29</td></tr><tr><td>0936013705</td><td>7824.6489.6</td><td rowspan="4">HE</td><td>M32x1.5</td></tr><tr><td>936013715</td><td>7824.6490.6</td><td>M40x1.5</td></tr><tr><td>936013671</td><td>7824.6475.6</td><td>Pg21</td></tr><tr><td>0936013682</td><td>7824.6476.6</td><td>Pg29</td></tr><tr><td>0936013707</td><td>7824.6489.8</td><td rowspan="4">HEHV</td><td>M32x1.5</td></tr><tr><td>0936013717</td><td>7824.6490.8</td><td>M40x1.5</td></tr><tr><td>0936013673</td><td>7824.6475.8</td><td>Pg21</td></tr><tr><td>0936013684</td><td>7824.6476.8</td><td>Pg29</td></tr><tr><td>0936013708</td><td>7824.6489.9</td><td rowspan="4">EMC</td><td>M32x1.5</td></tr><tr><td>0936013718</td><td>7824.6490.9</td><td>M40x1.5</td></tr><tr><td>0936013674</td><td>7824.6475.9</td><td>Pg21</td></tr><tr><td>0936013685</td><td>7824.6476.9</td><td>Pg29</td></tr></table>											TABLE 1		PRODUCTS TABLE			MATERIAL No.	Eng.No.	TYPE	D1	0936013704	7824.6489.5	STD	M32x1.5	0936013714	7824.6490.5	M40x1.5	0936013670	7824.6475.5	Pg21	0936013680	7824.6476.5	Pg29	0936013706	7824.6489.7	HV	M32x1.5	0936013716	7824.6490.7	M40x1.5	0936013672	7824.6475.7	Pg21	0936013683	7824.6476.7	Pg29	0936013705	7824.6489.6	HE	M32x1.5	936013715	7824.6490.6	M40x1.5	936013671	7824.6475.6	Pg21	0936013682	7824.6476.6	Pg29	0936013707	7824.6489.8	HEHV	M32x1.5	0936013717	7824.6490.8	M40x1.5	0936013673	7824.6475.8	Pg21	0936013684	7824.6476.8	Pg29	0936013708	7824.6489.9	EMC	M32x1.5	0936013718	7824.6490.9	M40x1.5	0936013674	7824.6475.9	Pg21	0936013685	7824.6476.9	Pg29										
TABLE 1		PRODUCTS TABLE																																																																																												
MATERIAL No.	Eng.No.	TYPE	D1																																																																																											
0936013704	7824.6489.5	STD	M32x1.5																																																																																											
0936013714	7824.6490.5		M40x1.5																																																																																											
0936013670	7824.6475.5		Pg21																																																																																											
0936013680	7824.6476.5		Pg29																																																																																											
0936013706	7824.6489.7	HV	M32x1.5																																																																																											
0936013716	7824.6490.7		M40x1.5																																																																																											
0936013672	7824.6475.7		Pg21																																																																																											
0936013683	7824.6476.7		Pg29																																																																																											
0936013705	7824.6489.6	HE	M32x1.5																																																																																											
936013715	7824.6490.6		M40x1.5																																																																																											
936013671	7824.6475.6		Pg21																																																																																											
0936013682	7824.6476.6		Pg29																																																																																											
0936013707	7824.6489.8	HEHV	M32x1.5																																																																																											
0936013717	7824.6490.8		M40x1.5																																																																																											
0936013673	7824.6475.8		Pg21																																																																																											
0936013684	7824.6476.8		Pg29																																																																																											
0936013708	7824.6489.9	EMC	M32x1.5																																																																																											
0936013718	7824.6490.9		M40x1.5																																																																																											
0936013674	7824.6475.9		Pg21																																																																																											
0936013685	7824.6476.9		Pg29																																																																																											
<table><tr><td>DOCUMENT STATUS</td><td>P1</td><td>RELEASE DATE</td><td>2021/06/09</td><td>09:04:20</td></tr></table>											DOCUMENT STATUS	P1	RELEASE DATE	2021/06/09	09:04:20																																																																															
DOCUMENT STATUS	P1	RELEASE DATE	2021/06/09	09:04:20																																																																																										
	10	9	8	7	6	5	4	3	2	1																																																																																				

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex 24B HOOD 4 PEGS HIGH CONSTRUCTION TOP ENTRY SERIES PRODUCT CUSTOMER DRAWING			
mm		1:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
ANGULAR TOL ± 1.0 °											
4 PLACES		±		EC NO: 666475				DOCUMENT NUMBER 936013704			
3 PLACES		±		DRWN: CRAODOREMS 2021/05/20							
2 PLACES		± 0.1		CHK'D: DMERONI 2021/06/07							
1 PLACE		± 0.2		APPR: MBIZZOZERO 2021/06/09				DOC TYPE		DOC PART	
0 PLACES		± 0.3		INITIAL REVISION:				REVISION			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				FIRST ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
						A3-SIZE		93601		CUSTOMER	
								SEE TABLE 1		GENERAL MARKET	
										SHEET NUMBER	
										2 OF 2	