

Quick Reference Guide AMPMODU System 50

The AMPMODU System 50 connector family includes a wide variety of high density board-to-board (through hole and surface mount) and cable-to-board connectors. AMPMODU System 50 receptacles and header assemblies can be categorized in three groups: board mount headers, board mount receptacles and cable-to-board receptacles. AMPMODU System 50 cable applied receptacles are available in ribbon cable or Flat Flexible Cable (FFC) cable termination. The variety of components and application possibilities, combined with small size and outstanding quality, make AMPMODU System 50 suitable for high density systems.

FEATURES AND BENEFITS

- Categorized in three groups: board mount headers, board mount receptacles, and cable-to-board receptacles
- Available in single and double row, vertical or rightangle, shrouded or unshrouded
- Formed from high conductivity copper alloy and selectively plated with gold for higher performance and reliability
- Housings on all board mounted assemblies are made of high-temperature tolerant materials and incorporate stand-offs for free drainage of flux cleaning solutions
- Integral latches for positive locking to shrouded mating headers
- · Suitable for high density systems
- RoHS compliant parts (Non-RoHS compliant parts available)

PRODUCT APPLICATIONS


- Medical equipment
- Gaming equipment
- Automotive controls
- Servers
- Test/measurement devices
- Factory automation
- Telecommunication equipment
- Storage equipment



Receptacles — Board-to-Board

Product Specification — 108-1093 **Application Specification** — 114-25031, 114-25035 (SMT)








RECEPTACLES — Through Hole Vertical			
	Part	Part Number	Positions
		5-104192-2	10
	Single Row	5-104192-4	15
		5-104192-7	30

RECEPTACLES — Through Hole Vertical		
Part	Part Number	Positions
	5-104078-3	10
Double Row	5-104078-2	40
	5-104078-8	100

RECEPTACLES — Surface Mount Vertical*			
Part	Part Number	Positions	
	5-104550-1	10	
Double Row	5-104550-2	20	
	5-104550-9	100	
·			




RECEPTACLES — Through Hole Right-Angle		
Part	Part Number	Positions
Single Row	5-104196-8	5
	5-104196-5	20
	5-104196-7	30




Through Hole Right-Angle		
Part	Part Number	Positions
Double Row	5-103911-1	10
	5-103911-5	40
	5-103911-8	100


RECEPTACLES -

Available AMPMODU Board-to-Board Configurations





Right-Angle



Parallel

Co-Planar




^{*}Surface mount parts are available in tubes or tape and reel packaging.

Headers — Board-to-Board



HEADERS — Through Hole Vertical		
Part	Part Number	Positions
Single Row Shrouded	5-104071-7	4
	5-104071-4	20
	6-104071-9	50



Through Hole Vertical		
Part	Part Number	Positions
Single Row Unshrouded	5-104178-1	4
	6-104178-3	25
	6-104178-9	50

HEADERS -




	HEADERS — Surface Mount Vertical*		
Part Number	Positions		
5-104549-1	10		
5-104549-2	20		
6-104549-0	100		
	5-104549-1 5-104549-2		


Product Specification — 108-1093 **Application Specification** — 114-25031, 114-25035 (SMT)



HEADERS — Through Hole Vertical		
Part	Part Number	Positions
Double Row Shrouded	5-104068-2	10
	6-104068-8	68
	1-104068-7	100



HEADERS — Through Hole Vertical		
Part	Part Number	Positions
Double Row Unshrouded	5-103916-3	8
	6-103916-1	40
	6-103916-7	100



HEADERS — Through Hole Vertical		
Part	Part Number	Positions
Double Row	5-104076-5	10
Shrouded w/ Card Slots	5-104076-8	100



^{*}Surface mount parts are available in tubes or tape and reel packaging.

Headers — Board-to-Board



HEADERS — Through Hole Right-Angle		
Part	Part Number	Positions
Single Row Unshrouded	5-104186-1	4
	6-104186-1	20
	6-104186-7	40




HEADERS — Through Hole Right-Angle				
Part	Part Number	Positions		
Single Row Shrouded	5-104074-7	4		
	5-104074-3	15		
	6-104074-9	50		

Product Specification — 108-1093 **Application Specification** — 114-25031



HEADERS — Through Hole Right-Angle					
Part	Part Number	Positions			
Double Row Unshrouded	5-104118-3	10			
	5-104746-2	22			
	5-104746-1	100			



Through Hole Right-Angle				
Part	Part Number	Positions		
Double Row Shrouded	5-104069-8	8		
	6-104069-8	68		
	6-104069-7	100		

Cable Assembly Receptacles

CABLE ASSEMBLY RECEPTACLES				
Part	Part Number	Positions		
Single Row Plain Receptacle Housing	487544-1	4		
Double Row Plain Receptacle Housing	487938-8	8		
Double Row FFC Receptacle Housing w/Latch	2-487937-0	20		
Single Row Plain Receptacle Housing	4-487544-7	50		
Double Row Ribbon Cable Receptacle	1-111196-1	50		
Paddleboard Ribbon Cable Receptacle	1-111595-1	50		
Double Row Plain Receptacle Housing	487938-1	100		
FFC Receptacle Contacts	1-487547-1	N/A		

Flat Flexible Cable (FFC) Connectors

Product Specification — 108-16022 **Application Specification** — 114-16008


Ribbon Cable Connectors Product Specification — 108-1109

Application Specification — 114-25029, 114-25040 (Paddleboard)











Questions that will help you better select the product that you need:

What is the available space?

0.050 centerline spacing for single row. 0.050 inch x 0.100 inch (between rows) centerline spacing for double row.

What is the Current rating (amp) requirement?

0.5 amp maximum for a single, crimped receptacle contact in free air, 88 V (operating voltage) — cable connector.
3.0 amp maximum for a single, contact in free air, 222 V (operating voltage) — board mounted connector.

What wire type and size requirements are there?

0.025 inch centerline ribbon cable having 30 AWG solid or stranded conductors or 32 AWG stranded conductors. 0.050 centerline Flat Flexible Cable (FFC) with 0.026 inch wide x 0.003 inch thick conductors.

What is the number of positions that are required?

4 through 50 positions for single row. 8 through 100 positions for double row.

What configuration/orientation is required?

Single/double row vertical and right-angle through hole. Double row vertical surface mount (SMT).

What is the operating temperature requirements?

-65° C to 105° C range

What are the environmental considerations?

Refer to TE Connectivity Product Specifications 108-1093 (board-to-board) and 108-1109 (cable-to-board).

FOR MORE INFORMATION

TE Technical Support Center

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 +52 (0) 55-1106-0800 Mexico Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 Netherlands: +31(0) 73-6246-999 China: +86 (0) 400-820-6015

Part numbers in this brochure are RoHS Compliant*, unless marked otherwise.

*as defined www.te.com/leadfree

te.com

© 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved. 9-1773462-2 CIS LUG FP 1M 10/2011

AMPMODU, TE Connectivity and the TE connectivity (logo) are trademarks. Other logos, product and company names mentioned herein may be trademarks of their respective owners.

