



2 YEARS
MANUFACTURER
GUARANTEE



Product number 1173750005
EAN 4007123684670

TECHNICAL DATA

Luminous flux	400 lm
Power consumption	5 W
Colour temperature	6000 K
Colour rendering index	70-79 (class 2 A)
Lifetime	50000 h
Battery capacity	2 Ah
Light duration max.	29 h

Battery charging time approx.	3.5 h
Number of batteries	1
Battery type	18650
Battery technology	Lithium-ion
Protection class	III
Degree of protection (IP)	IP44
Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	0.12 kg
Dimension LxWxH (without packing)	2.9 cm x 2.9 cm x 11.5 cm

Weight of product (including packaging)	0.21 kg
Dimension LxWxH (incl. packing)	8.8 cm x 6.5 cm x 17.7 cm