

| | | | |
|----------------------|-------|----------------------|------------|
| MC20805A6W-GPR-V2 | 2 x 8 | 5mm Character Height | LCD Module |
| Specification | | | |
| Version: 1 | | Date: 29/09/2016 | |
| Revision | | | |
| | | | |

| Display Features | | | | | |
|-----------------------|-------------------------|---|--|--------------|------------------|
| Character Count | 2 x 8 |  | | | |
| Appearance | Black on Grey | | | | |
| Logic Voltage | 5V | | | | |
| Interface | Parallel | | | | |
| Font Set | English / Japanese | | | | |
| Display Mode | Reflective | | | | |
| Character Height | 5.56mm | | | | |
| LC Type | STN | | | | |
| Module Size | 58.00 x 32.00 x 9.50 mm | | | | |
| Operating Temperature | -20°C ~ +70°C | | | | |
| Construction | COB | | | Box Quantity | Weight / Display |
| LED Backlight | --- | | | 45 pcs | 28.88 grams |

* - For full design functionality, please use this specification in conjunction with the ST7066U specification. (Provided Separately)

| Display Accessories | |
|--------------------------|--|
| Part Number | Description |
| MCCMDB-16DIL | LCD Interconnect board, can be driven from either a PC or a single Board computer with a USB output. |
| MCCBL1A16DLIP-16DILS-150 | 16 Way, Dual in-line to Dual In-line connector Cable. |
| | |

| Optional Variants | | |
|-------------------|-------------|---------|
| Fonts | Appearances | Voltage |
| | | |




Pin Layout


| PI | SYMBOL | DESCRIPTION | REMARKS |
|----|--------|------------------------|---------|
| 1 | Vss | GND | |
| 2 | Vdd | Power supply for LCM | 5.0V |
| 3 | V | Contrast Adjust | |
| 4 | RS | Register Select Signal | |
| 5 | R/W | Data Read / Write | |
| 6 | E | Enable Signal | |
| 7 | DB0 | Data bus line | |
| 8 | DB1 | Data bus line | |
| 9 | DB2 | Data bus line | |
| 10 | DB3 | Data bus line | |
| 11 | DB4 | Data bus line | |
| 12 | DB5 | Data bus line | |
| 13 | DB6 | Data bus line | |
| 14 | DB7 | Data bus line | |
| 15 | NC | No Connection | 5.0V |
| 16 | NC | No Connection | |

MIDAS
DISPLAYS

Block Diagram



Power Supply Diagram



| | | | |
|----------------------|-------|----------------------|------------|
| MC20805A6W-GPR-V2 | 2 x 8 | 5mm Character Height | LCD Module |
| Specification | | | |
| Version: 1 | | Date: 29/09/2016 | |
| Revision | | | |
| | | | |



Font Map

| Upper 4bit Lower 4bit | LLLL | LLLH | LLHL | LLHH | LHLL | LHLH | LHHL | LHHH | HLLL | HLLH | HLHL | HLHH | HHLL | HHLH | HHHL | HHHH |
|--------------------------------|------------------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| LLLL | CG RAM (1) | | | | | | | | | | | | | | | |
| LLLH | (2) | | | | | | | | | | | | | | | |
| LLHL | (3) | | | | | | | | | | | | | | | |
| LLHH | (4) | | | | | | | | | | | | | | | |
| LHLL | (5) | | | | | | | | | | | | | | | |
| LHLH | (6) | | | | | | | | | | | | | | | |
| LHHL | (7) | | | | | | | | | | | | | | | |
| LHHH | (8) | | | | | | | | | | | | | | | |
| HLLL | (1) | | | | | | | | | | | | | | | |
| HLLH | (2) | | | | | | | | | | | | | | | |
| HLHL | (3) | | | | | | | | | | | | | | | |
| HLHH | (4) | | | | | | | | | | | | | | | |
| HHLL | (5) | | | | | | | | | | | | | | | |
| HHLH | (6) | | | | | | | | | | | | | | | |
| HHHL | (7) | | | | | | | | | | | | | | | |
| HHHH | (8) | | | | | | | | | | | | | | | |

| | | | |
|----------------------|-------|----------------------|------------|
| MC20805A6W-GPR-V2 | 2 x 8 | 5mm Character Height | LCD Module |
| Specification | | | |
| Version: 1 | | Date: 29/09/2016 | |
| Revision | | | |
| Page 4 of 5 | | | |



Absolute Maximum Ratings

| Item | Symbol | Condition | Min | Typ | Max | Unit |
|-----------------------|--------|-----------|-----------|-----|----------|------|
| Power Supply (LOGIC) | Vdd | 25 °C | -0.3 | --- | 7.0 | V |
| Power Supply (LCD) | V0 | 25 °C | Vdd -13.5 | --- | Vdd +0.3 | V |
| Input Voltage | Vin | 25 °C | -0.3 | --- | Vdd +0.3 | V |
| Operating Temperature | Vopr | --- | -20 | --- | 70 | °C |
| Storage Temperature | Vstg | --- | -30 | --- | 80 | °C |

Electronic Characteristics

| Item | Symbol | Condition | Min | Typ | Max | Unit |
|-------------------------------|-------------------|-----------|------|------|-------|------|
| Input Voltage | Vlcm = Vdd | --- | --- | 5.0 | --- | V |
| Supply Current | Idd | Vdd=5V | --- | 1.5 | --- | mA |
| Driving Voltage for LCD Panel | Vlcd = (Vdd - V0) | -20 °C | 4.40 | --- | 4.90 | V |
| | | 0 °C | 4.30 | --- | 4.9€ | |
| | | 25 °C | 4.25 | 4.50 | 4.85 | |
| | | 50 °C | 4.10 | --- | 4.80 | |
| | | 70 °C | 4.05 | --- | 4.ĩ 5 | |

LCD Characteristics

| For STN/FSTN LCD Panel Types | | | | | | |
|------------------------------|-------------------|-----------|-----|-----|-----|------|
| Item | Symbol | Condition | Min | Typ | Max | Unit |
| Viewing Angle | $\Phi 2 - \Phi 1$ | K = 4 | 40° | --- | --- | Deg |
| | Θ | | 60° | | | |
| Contrast Ratio | K | --- | --- | 10 | --- | --- |
| Response Time (Rise) | TR | --- | --- | 150 | 250 | ms |
| Response Time (Fall) | TF | --- | --- | 150 | 250 | ms |

DESIGN • MANUFACTURE • SUPPLY

| | | | |
|----------------------|-------|----------------------|------------|
| MC20805A6W-GPR-V2 | 2 x 8 | 5mm Character Height | LCD Module |
| Specification | | | |
| Version: 1 | | Date: 29/09/2016 | |
| Revision | | | |
| | | | |

