

# KRYTECH 511

## DESCRIPTION AND GENERAL PROPERTIES

- **Material** Water-based polymer
- **Length (cm)** 23 - 27
- **Wrist** Knitted wrist
- **Colour/Color** Green
- **Interior finish** Seamless textile support from HDPE fibres
- **Exterior finish** Ventilated back
- **Size / EAN** 7 8 9 10 11
- **Packaging** 1 pair/bag - 12 pairs/bag - 96 pairs/carton
- **Complementary information** Silicone and DMF Free  
OEKO-TEX®



## PERFORMANCE RESULTS

### Certification category 2



4341

### Legends



**MECHANICAL  
HAZARDS  
EN 388**

PERFORMANCE LEVELS

0-4 0-5 0-4 0-4  
 └─ Puncture resistance  
 └─ Tear resistance  
 └─ Blade cut resistance  
 └─ Abrasion resistance



**LOW CHEMICAL  
PROTECTION  
EN 374**



**MICRO-ORGANISMS  
EN 374**



**RADIOACTIVE  
CONTAMINATION  
EN 421**



**HEAT  
AND FIRE  
EN 407**

PERFORMANCE LEVELS

0-4 0-4 0-4 0-4 0-4 0-4  
 └─ Resistance to large quantities of molten metal  
 └─ Resistance to small drops of molten metal  
 └─ Radiant heat resistant  
 └─ Convective heat resistance  
 └─ Contact heat resistance  
 └─ Burning behaviour



**SPECIFIC CHEMICAL  
PROTECTION  
EN 374**

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofurane
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%



**COLD HAZARDS  
EN 511**

PERFORMANCE LEVELS

0-4 0-4 0 or 1  
 └─ Water permeability  
 └─ Contact cold resistance  
 └─ Convective cold resistance

For more details: [www.mapa-pro.com](http://www.mapa-pro.com)

# KRYTECH 511

## DESCRIPTION AND GENERAL PROPERTIES

- Breathable coating to have better comfort in use
- Cut protection for safety work
- Anatomical shape: close fit for precision
- Durable for a long-wear

## MAIN FIELDS OF USE

### Automotive/mechanical industry

- Assembly of small parts
- Automotive assembly
- Bodywork assembly
- Finishing sharp parts
- Handling sheet metal
- Machine tool manufacture
- Mechanical maintenance

### Mechanical industry

- Handling sharp sheet metal
- Precision assembly

### Other industries

- Machine maintenance

## INSTRUCTIONS FOR USE

### Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use in the workplace may differ from the tests performed in the laboratory.  
It is not recommended for persons sensitised to natural latex( wrist with elastic natural rubber)  
It is not recommended to use this glove next to moving machinery.
- Put the gloves on dry, clean hands.
- Ensure the insides of the gloves are dry before putting them on again.

### Storage conditions

Store the gloves in their original packaging protected from heat, light and humidity

### Laundering conditions

Caution : using the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels.

## LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate

0075/014/162/04/16//0398

- Issued by the notified body nr

CTC - 4 rue Hermann Frenkel -69367 Lyon cedex 07 -France

0075