

# Eaton 260154

Catalog Number: 260154

Eaton Moeller series NZM - Molded Case Circuit Breaker. Delay unit

General specifications



Product Name	Catalog Number
Eaton Moeller series NZM release	260154

EAN	Product Length/Depth
4015082601546	100 mm

Product Height	Product Width
114 mm	74 mm

Product Weight	Compliances
0.847 kg	IEC
	RoHS conform

## Product specifications

### Used with

N(S)1(-4), 2(-4), 3(-4), 4(-4)

50/60 Hz

220 V - 240 V

380 V - 440 V

480 V - 550 V

DC/AC

24 V

NZM1(-4), 2(-4), 3(-4), 4(-4) N(S)1(-4), 2(-4), 3(-4), 4(-4) 50/60 Hz 220 V - 240 V 380 V - 440 V 480 V - 550 V DC/AC 24 V

### Type

Accessory Undervoltage release Undervoltage release, off-delayed

### Special features

Delay unit for combination with special undervoltage releases. For use with emergency-stop devices in connection with an emergency-stop button. not UL/CSA approved Voltage dips of less than the setting between 0.06 – 16 s do not cause disconnection of the NZM circuit-breaker or N switch-disconnector. Delay time can be set from: 70 ms – 4 s. With additional external capacitor: 30,000  $\mu$ F 35 V to 8 s, 90,000  $\mu$ F 35 V to 16 s. A special release is required. Cannot be installed simultaneously with separate NZM...-XHIV early-make auxiliary contact or NZM...-XA... shunt release. Delay unit for separate installation. Fixing: top-hat rail or screws. For other operating voltages use a control transformer.

### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

## Resources

### Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

### Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

### Declarations of conformity

[DA-DC-03\\_UVU-NZM](#)

### Drawings

[eaton-circuit-breaker-undervoltage-nzm-delay-unit-dimensions.eps](#)

### eCAD model

[DA-CE-ETN.UVU-NZM](#)

### Installation instructions

[eaton-undervoltage-release-off-delayed-nzm-1-2-3-4-il01219005z.pdf](#)

### Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

### Technical data sheets

[eaton-nzm-technical-information-sheet](#)

#### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

#### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

#### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Electric connection type

Screw connection

#### Frame

NZM1/2/3/4

#### Number of contacts (normally open contacts)

0

#### Rated control supply voltage (Us) at AC, 50 Hz - max

550 V

#### Rated control supply voltage (Us) at AC, 50 Hz - min

24 V

#### Rated control supply voltage (Us) at AC, 60 Hz - max

550 V

#### Rated control supply voltage (Us) at AC, 60 Hz - min

24 V

#### Voltage rating at AC

220 - 550 V AC

#### Voltage rating at DC

24 V DC

#### Suitable for

Off-load switch

#### Connection type

With bolt connection

#### Delay time

70 - 4000 ms (undervoltage releases, off-delayed)

#### Voltage type

AC/DC

#### Delay time with additional external capacitor

8 s (30 mF)

16 s (90 mF)

#### Rated operation current (Ie)

< 0.5 A

#### Functions

Delayed

#### Terminal capacity (solid/flexible conductor)

20 - 14 AWG (1x) at shunt release

20 - 16 AWG (2x) at shunt release

0.5 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (2x) at shunt release with ferrule

0.5 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (2x) for undervoltage releases, off-delayed

with ferrule

0.5 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1x) at shunt release with ferrule

18 - 14 AWG (1x) for undervoltage releases, off-delayed

0.5 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1x) for undervoltage releases, off-delayed

with ferrule

#### Power consumption

50 VA

#### Rated control supply voltage (Us) at DC - max

24 V

#### Rated control supply voltage (Us) at DC - min

24 V

#### Number of contacts (normally closed contacts)

0

#### Number of contacts (change-over contacts)

0

#### Undelayed short-circuit release - min

0 A

#### Undelayed short-circuit release - max

0 A



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia