



# CSX-WNF1141252ZZZZ

CSS/CSX High Speed

**COLOR SENSORS** 





Illustration may differ



### Ordering information

Туре	Part no.
CSX-WNF1141252ZZZZ	1120178

Other models and accessories → www.sick.com/CSS\_CSX\_High\_Speed

### Detailed technical data

### **Features**

Dimensions (W x H x D)	30 mm x 53 mm x 78.5 mm
Sensing distance	13 mm
Sensing distance tolerance	± 5 mm
Housing design	X housing
Light source	LED, RGB <sup>1)</sup>
LED risk group marking	1
Wave length	460 nm, 530 nm, 625 nm
Light emission	Long side of housing
Light spot size	2 mm x 4 mm
Light spot direction	Vertical <sup>2)</sup>
Teach-in mode	Single value teach-in Multi value teach-in
Color mode	C (Color) C + I (Color + Illumination)
Output mode	2 colors in standard mode/best fit mode 3 colors in coded mode
Adjustment of the sensitivity	Continuous: 0 999
Available job banks	4
Output (channel)	2 × hardware switching outputs
Parameter presettings	None

 $<sup>^{1)}</sup>$  Average service life: 100,000 h at  $T_U$  = +25 °C.

<sup>&</sup>lt;sup>2)</sup> In relation to long side of housing.

### Mechanics/electronics

Supply voltage	10.8 V DC 28.8 V DC $^{1)}$
Ripple	$\leq$ 5 $V_{pp}^{2}$
Current consumption	< 120 mA <sup>3)</sup>
Switching frequency	13.8 kHz
Response time	36 µs
Jitter	18 μs
Switching output	NPN
Switching output (voltage)	NPN: HIGH = $V_S$ / LOW $\leq 3 \text{ V}$
Output current I <sub>max.</sub>	100 mA <sup>4)</sup>
Input, teach-in (ET)	Teach: U < 2 V
Input, blanking input (AT)	Blanked: U < 2 V
Retention time (ET)	3 s, non-volatile memory
Connection type	Male connector M12, 5-pin
Protection class	III
Circuit protection	U <sub>V</sub> connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Enclosure rating	IP67
Weight	94 g
Housing material	VISTAL®
Optics material	PMMA

 $<sup>^{1)}</sup>$  Limit values: DC 12 V (-10 %) ... DC 24 V (+20 %) . Operation in short-circuit protected network max. 8 A.

### Communication interface

ı	Digital output	$Q_1, Q_2$
	Number	2
ı	Digital input	$ln_1$ , $ln_2$
	Number	2

### Ambient data

Ambient operating temperature	-20 °C +60 °C
Ambient temperature, storage	-25 °C +75 °C
Shock load	According to IEC 60068-2-27 (30 g/11 ms)
UL File No.	E181493

### Connection type/pinouts

Connection type	Male connector M12, 5-pin
Pinouts	
BN 1	+ (L+)
WH 2	$Q_{L2}/IN_1$
BU 3	- (M)

 $<sup>^{2)}</sup>$  May not fall below or exceed U<sub>V</sub> tolerances.

<sup>&</sup>lt;sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Total current of all Outputs.

# CSX-WNF1141252ZZZZ | CSS/CSX High Speed

**COLOR SENSORS** 


BK 4	$Q_{L1}$
GY 5	$\ln_2$


### Classifications


ECLASS 5.0 27270907 ECLASS 6.0 27270907 ECLASS 6.2 27270907 ECLASS 7.0 27270907 ECLASS 8.0 27270907 ECLASS 8.1 27270907 ECLASS 9.0 27270907 ECLASS 10.0 27270907 ECLASS 10.0 27270907 ECLASS 11.0 27270907 ECLASS 11.0 27270907 ECLASS 12.0 27270907 ETIM 5.0 ECO01817 ETIM 6.0 ECO01817 ETIM 8.0 ECO01817 UNSPSC 16.0901 39121528		
ECLASS 6.0 27270907 ECLASS 6.2 27270907 ECLASS 7.0 27270907 ECLASS 8.0 27270907 ECLASS 8.1 27270907 ECLASS 9.0 27270907 ECLASS 10.0 27270907 ECLASS 10.0 27270907 ECLASS 11.0 27270907 ECLASS 11.0 27270907 ECLASS 12.0 27270907 ETIM 5.0 EC001817 ETIM 6.0 EC001817 ETIM 7.0 EC001817	ECLASS 5.0	27270907
ECLASS 6.2 27270907 ECLASS 7.0 27270907 ECLASS 8.0 27270907 ECLASS 8.1 27270907 ECLASS 9.0 27270907 ECLASS 10.0 27270907 ECLASS 11.0 27270907 ECLASS 11.0 27270907 ECLASS 12.0 27270907 ETIM 5.0 EC001817 ETIM 6.0 EC001817 ETIM 7.0 EC001817	ECLASS 5.1.4	27270907
ECLASS 7.0 27270907 ECLASS 8.0 27270907 ECLASS 8.1 27270907 ECLASS 9.0 27270907 ECLASS 10.0 27270907 ECLASS 11.0 27270907 ECLASS 12.0 27270907 ETIM 5.0 EC001817 ETIM 6.0 EC001817 ETIM 7.0 EC001817 ETIM 8.0 EC001817	ECLASS 6.0	27270907
ECLASS 8.0 27270907 ECLASS 8.1 27270907 ECLASS 9.0 27270907 ECLASS 10.0 27270907 ECLASS 11.0 27270907 ECLASS 12.0 27270907 ETIM 5.0 EC001817 ETIM 6.0 EC001817 ETIM 7.0 EC001817 ETIM 8.0 EC001817	ECLASS 6.2	27270907
ECLASS 8.1 27270907 ECLASS 9.0 27270907 ECLASS 10.0 27270907 ECLASS 11.0 27270907 ECLASS 12.0 27270907 ETIM 5.0 EC001817 ETIM 6.0 EC001817 ETIM 7.0 EC001817 ETIM 8.0 EC001817	ECLASS 7.0	27270907
ECLASS 9.0 27270907 ECLASS 10.0 27270907 ECLASS 11.0 27270907 ECLASS 12.0 27270907 ETIM 5.0 EC001817 ETIM 6.0 EC001817 ETIM 7.0 EC001817 ETIM 8.0 EC001817	ECLASS 8.0	27270907
ECLASS 10.0 27270907 ECLASS 11.0 27270907 ECLASS 12.0 27270907 ETIM 5.0 EC001817 ETIM 6.0 EC001817 ETIM 7.0 EC001817 ETIM 8.0 EC001817	ECLASS 8.1	27270907
ECLASS 11.0       27270907         ECLASS 12.0       27270907         ETIM 5.0       EC001817         ETIM 6.0       EC001817         ETIM 7.0       EC001817         ETIM 8.0       EC001817	ECLASS 9.0	27270907
ECLASS 12.0 27270907 ETIM 5.0 EC001817 ETIM 6.0 EC001817 ETIM 7.0 EC001817 ETIM 8.0 EC001817	ECLASS 10.0	27270907
ETIM 5.0 EC001817 ETIM 6.0 EC001817 ETIM 7.0 EC001817 ETIM 8.0 EC001817	ECLASS 11.0	27270907
ETIM 6.0 EC001817 ETIM 7.0 EC001817 ETIM 8.0 EC001817	ECLASS 12.0	27270907
ETIM 7.0 EC001817 ETIM 8.0 EC001817	ETIM 5.0	EC001817
EC001817	ETIM 6.0	EC001817
	ETIM 7.0	EC001817
UNSPSC 16.0901 39121528	ETIM 8.0	EC001817
	UNSPSC 16.0901	39121528

### Dimensional drawing (Dimensions in mm (inch))

Dimensional drawing, sensor








- ① Optical axis
- ② Fixing hole
- 3 M12 male connector, delivery state
- ④ M12 male connector, end stop right
- ⑤ M12 male connector, end stop left
- Sensing distance
- ⑦ Display and adjustment elements

### **Pinouts**

Pinouts, see table Technical data: Connection type/pinouts




Male connector, M12, 5-pin, A-coded

**COLOR SENSORS** 

### Adjustments

Display and adjustment elements



- ① LEDs (status display)
- ② 7-segment display
- ③ Plus/minus button

### Recommended accessories

Other models and accessories → www.sick.com/CSS\_CSX\_High\_Speed

	Brief description	Туре	Part no.
Universal bar clamp systems			
	Plate K for universal clamp bracket, steel, zinc coated, Universal clamp (2022726), mounting hardware	BEF-KHS-K01	2022718
	Mounting bar, straight, 200 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12G-A	4056054
	Mounting bar, L-shaped, 150 mm x 150 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12L-A	4056052
Others			
	Connection type head A: Male connector, M12, 5-pin, straight, A-coded     Description: Unshielded, Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: -     Connection systems: Screw-type terminals     Permitted cross-section: ≤ 0.75 mm²     Note: For field bus technology	STE-1205-G	6022083
	<ul> <li>Connection type head A: Female connector, M12, 5-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 5-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals, Uncontaminated zones</li> </ul>	YF2A15- 050VB5XLEAX	2096240

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

