




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
PCB Thickness (Recommended): **1.57 mm [.062 in]**
Mating Tab Width: **4.75 mm [.187 in]**
Mating Tab Thickness: **.51 mm [.02 in]**
PCB Hole Diameter: **1.32 mm [.052 in]**

Features

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

PCB Contact Termination Area Plating Material Thickness	3.81 μm[150 μin]
Contact Underplating Material Thickness	1.27 μm[50 μin]
Contact Mating Area Plating Material Thickness	3.81 μm[150 μin]
PCB Terminal Type	Tab
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Plating Material	Tin
Contact Underplating Material	Nickel
Terminal Size	4.75
Terminal Orientation	Right Angle

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------



Product Terminates To

Printed Circuit Board

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Extension Below Board	3.81 mm[.15 in]
Terminal Material Thickness	.51 mm[.02 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
PCB Hole Diameter	1.32 mm[.052 in]
Profile Height from PCB	7.47 mm[.298 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1217121-1 110 FASTON,PCB TAB,TPBR	 TE Part # 1-1217056-0 250 FASTON,PCB TAB,TPBR	 TE Part # 62705-1 187 FASTON TAB TPBR	 TE Part # 1742803-1 FASTON 312 PCB TAB TPBR
 TE Part # 1217057-1 187 FASTON,PCB TAB,TPBR	 TE Part # 62437-1 110 FASTON TAB TPBR	 TE Part # 1217756-1 187 FASTON,TAB,TNBR	 TE Part # 63982-1 187 FASTON TAB TPBR
 TE Part # 1-725996-2 110 FASTON,FLAG,PCB TAB,TPBR	 TE Part # 62747-1 FASTON 187 TAB STAKE TPBR	 TE Part # 60284-2 205 FASTON TAB TPBR	 TE Part # 1742188-1 250 FASTON,PCB TAB,TCBR
 TE Part # 1217167-1 250 FASTON,PCB TAB,TCBR	 TE Part # 1217169-1 250 FASTON,PCB TAB,TCBR	 TE Part # 725996-2 110 FASTON TAB TPBR	

Also in the Series | FASTON 187



Crimp Terminal Housings(40)



Insertion & Extraction Tools(1)



Insulation Boots & Sleeves(1)



Joints & Splices(1)



PCB Terminals(42)




Quick Disconnects(205)



Splices(1)

Customers Also Bought



TE Part #172162-1
12 CIR UNIV M-N-L CAP



TE Part #172158-1
3 CIR UNIV M-N-L CAP



TE Part #1-2329383-1
PB OFF/ON FC BLK M3 TERM. IP68



TE Part #1827691-3
DYNATAP 3200 TAP ASSY 24P
BOTTOM MOUNT



TE Part #1-1903131-0
DYNAMIC 1200D TAB HSG 20P P/M



TE Part #2329387-4
PB OFF/ON FC BLK M1 TERM GRE
LED IP68



TE Part #2199248-4
Shield Finger, Loose Piece, Type A, 1.0
h



TE Part #CAT-HST-HFT5000
HFT5000 Heat Shrink Tubing

Documents

Product Drawings

187 FASTON,PCB TAB,TNBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1217156-1_D_c-1217156-1-d.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1217156-1_D_c-1217156-1-d.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1217156-1_D_c-1217156-1-d.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON PCB Tabs and Receptacles](#)

English

[PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English