


# REPORT

## 34 Series



**finder**<sup>®</sup>  
SWITCH TO THE FUTURE

**NEW**



Approvals (according to type)




## Ultra-Slim Solid State PCB relays (SSR)

### Type 34.81.7.xxx.xxxx

1 Pole from 0.1 to 6 A  
Ultra slim, 5 mm wide.  
PCB or 93 series sockets  
mounting.  
Silent, high speed switching  
with long electrical life.


### Features

- Single circuit output switching options: - 6 A, 24 V DC  
- 0.1 A, 48 V DC  
- 0.2 A, 110/220 V DC  
- 2 A, 240 V AC
- Printed circuit mount - direct or via PCB socket
- 35 mm rail mount - via screw, screwless or push-in terminal sockets
- Sensitive DC Input circuits (Dual AC/DC input drive possible using 93 series sockets)
- Wash tight: RT III



**Type 34.81.7.xxx.9024**

- Rated output voltage: 24 V DC
- Switching output voltage range: 1.5...33 V
- Rated current (single mounting): 6 A
- Rated current (group socket mounting): 4 A (50 °C)  
3 A (70 °C)
- Max. peak current (10ms): 50 A



**Type 34.81.7.xxx.7048**

- Rated output voltage: 48 V DC
- Switching output voltage range: 1.5...53 V
- Rated current (single mounting): 100 mA
- Rated current (group socket mounting): 100 mA
- Max. peak current (10ms): 0.5 A



**Type 34.81.7.xxx.7220**

- Rated output voltage: 110/220 V DC
- Switching output voltage range: 90...256 V
- Rated current (single mounting): 200 mA
- Rated current (group socket mounting): 200 mA
- Max. peak current (10ms): 10 A



**Type 34.81.7.xxx.8240**

- Rated output voltage: 240 V AC
- Switching output voltage range: 12...275 V
- Repetitive peak off-state voltage: 800 V
- Rated current (single mounting): 2 A (50°C)  
1.5 A (70°C)
- Rated current (group socket mounting): 750 mA (50°C)  
450 mA (70°C)
- Max. peak current (10ms): 80 A

Type		34.81.7.005.9024 34.81.7.005.8240*	34.81.7.012.9024 34.81.7.012.8240*	34.81.7.024.9024 34.81.7.024.7048 34.81.7.024.7220 34.81.7.024.8240*	34.81.7.060.9024 34.81.7.060.7048 34.81.7.060.7220 34.81.7.060.8240*
Nominal input voltage	V	5	12	24	60
Operating input range	V	3.5...12	8...17	16...30	35...72
Nominal absorption	mA	7/ 12*	7	7	3.5
Power absorption	mW	35/60*	85	170	210
Ambient temperature range	°C	-20...+70/-20...+50*	-20...+70/-20...+50*	-20...+70/-20...+50*	-20...+70/-20...+50*
Environmental protection		RTIII	RTIII	RTIII	RTIII

FINDER reserves the right to alter characteristics at any time without notice.FINDER assumes no liability for damage to persons or property, caused as a result of the incorrect use or application of its products.