

Specifications for BMP41/BMP51/BMP53 Labelmaker Labels

Adhesive	Permanent Acrylic
Application	Automation & Electrical Component Markers; Bin & Storage Identification; General & Industrial Identification
Approval/Compliance	UL Recognised; CSA Accepted
Article No.	143241
Brady Material No.	B-422
Material Type	Polyester
Brand	ToughBond™ Series
Colour	Black on White
Finish	Gloss
Description	Designed to withstand solvent exposure. UL rated for surfaces commonly used in solar panel manufacturing. Also used for component identification, punch block & patch panel labels, asset and inventory tracking. Please Note: This material is UL & CSA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.
Max. Service Temp. °C	100
Order Reference	M-7-422
Printer Compatibility	BMP41; BMP51; BMP53
Shape	Square
Size - Height (mm)	12.70
Size - Width (mm)	12.70
Additional Information	Port Labels
Total Qty per Pack	280 Label(s) / Box
Voice/Data Application	Faceplate & Outlet; Punch Block & Patch Panel; Data Centre Equipment; Bay, Rack & Frame Labels; Individual Port Labels
Industry	Data & Telecommunications; Electrical; Facility & Safety Industry; General Industry; Manufacturing; Process
Min. Service Temp. °C	-40
Thickness (mm)	0.1016