



### Auxiliary contact characteristics

Type of contact		1 C/O
IEC Conventional free air thermal current $I_{th} \leq 40^\circ\text{C}$	A	5
Rated insulation voltage $U_i$ IEC/EN	V	250
Min. conductivity		5V 160mA 30V 30mA


### Mechanical features

Tightening torque for terminals	min	Nm	0.8
	max	Nm	1
	min	lbin	7
	max	lbin	9

Conductor section	AWG/Kcmil	min		20
		max		16
Flexible w/o lug conductor section		min	mm <sup>2</sup>	0.5
		max	mm <sup>2</sup>	1.5
Flexible c/w lug conductor section		min	mm <sup>2</sup>	0.5
		max	mm <sup>2</sup>	1.5

Terminals	type	Screw
	tool	PZ2

Weight	g	40
--------	---	----



### Wiring diagrams

### Certifications and compliance

### Certificates

### ETIM classification

EC000066 - Power contactor, AC switching