



Product designation				Changeover Switch
Product type designation				GLC
Number of poles	Nr.			4
Operating voltage type				AC
<b>Contact characteristics</b>				
IEC Conventional free air thermal current $I_{th} \leq 40^\circ\text{C}$	A			800
Rated insulation voltage $U_i$ IEC/EN	V			1000
Rated impulse withstand voltage $U_{imp}$	kV			12
Operating current $I_e$				
AC-31B	400V	A	800	
	500V	A	800	
	690V	A	800	
AC-32B	400V	A	800	
	500V	A	800	
	690V	A	800	
AC-33B	400V	A	800	
	500V	A	800	
	690V	A	800	
Power dissipation per pole max	W			40
Rated operational power AC23A	400V	kW	400	
	690V	kW	800	
Rated short time current (1s) $I_{cw}$ (rms)	kA			20
Conditional short-circuit current (rms)	kA			80
Short-circuit protection with fuse	Class/A			gG/800
Making capacity AC23A 400V	A			8000
Breaking capacity AC23A 400V	A			6400
Mechanical life	cycles			5000
<b>Mechanical features</b>				
Operating position	normal allowable		Vertical plan Any	
Fixing	Screw			
Terminals	type			M12 x 40
Tightening torque for terminals	min	Nm	50	
	max	Nm	75	
	min	lbin	442	
	max	lbin	664	
Conductor section				

IEC min	mm <sup>2</sup>	2x185
IEC max	mm <sup>2</sup>	4x300
AWG/kcmil min		2
AWG/kcmil max	kcmil	4x600

**Ambient conditions**

Operating temperature

min	°C	-25
max	°C	+55


Storage temperature

min	°C	-40
max	°C	+70


Max altitude

m	3000
---	------

**Dimensions**



**Wiring diagrams**



**Certifications and compliance**

Compliance

IEC/EN 60947-1
IEC/EN 60947-3
IEC/EN 60947-6-1

**ETIM classification**

ETIM 8.0

EC000216 -  
Switch  
disconnecter