



Brand of NTN corporation

## Technical data

### 22312EF800


Spherical roller bearings



Spherical roller bearing for vibratory applications, one-piece machined cage, groove and lubrication holes on outer ring, special C4 class clearance

**ULTAGE**

#### VISUAL (S)



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15



PRODUCT DEFINITION

|                                   |            |
|-----------------------------------|------------|
| Brand                             | SNR        |
| d - Internal diameter             | 60 mm      |
| D - External diameter             | 130 mm     |
| B - Bearing/Inner ring width      | 46 mm      |
| d2 - External diameter inner ring | 0 mm       |
| D1 - Inner diameter outer ring    | 111,9 mm   |
| rs - Min fillet radius            | 2,1 mm     |
| Number of lubrication holes       | 3          |
| b - Groove width                  | 9 mm       |
| k - Hole diameter                 | 4 mm       |
| Radial clearance class            | C4 Special |
| Mass                              | 2,892 kg   |

PRODUCT PERFORMANCE



## PRODUCT PERFORMANCE

|                                           |              |
|-------------------------------------------|--------------|
| <b>C - Dynamic load</b>                   | 340000000 mN |
| <b>C0 - Static load</b>                   | 319000000 mN |
| <b>Cu - Fatigue limit load</b>            | 38900000 mN  |
| <b>e - Coefficient</b>                    | 0.35         |
| <b>Y0 - Static axial load coefficient</b> | 1.91         |
| <b>Y1 - Lower axial load coefficient</b>  | 1.95         |
| <b>Y2 - Upper axial load coefficient</b>  | 2.9          |
| <b>N ref - Reference thermal speed</b>    | 25800 °/s    |
| <b>N lim - Mechanical Limit Speed</b>     | 30600 °/s    |
| <b>Tmin - Min operating temperature</b>   | 233,15 °K    |
| <b>Tmax - Max operating temperature</b>   | 473,15 °K    |

## BEARING FREQUENCIES

|                                                                 |          |
|-----------------------------------------------------------------|----------|
| <b>BPFO - Over rolling frequency on outer ring (60 rpm)</b>     | 5.625 Hz |
| <b>BPFI - Over rolling frequency on inner (60 rpm)</b>          | 8.375 Hz |
| <b>BSF - Over rolling frequency on rolling element (60 rpm)</b> | 4.768 Hz |
| <b>BRF - Rotational frequency - rolling element (60 rpm)</b>    | 2.384 Hz |
| <b>FTF - Rotational frequency - cage (60 rpm)</b>               | 0.402 Hz |

## ABUTMENT

|                                                       |        |
|-------------------------------------------------------|--------|
| <b>da max - Max shoulder diameter IR</b>              | 0 mm   |
| <b>da min - Min shoulder diameter IR</b>              | 72 mm  |
| <b>Da max - Max shoulder diameter OR</b>              | 118 mm |
| <b>ra max - Max shaft &amp; housing fillet radius</b> | 2 mm   |



## INDUSTRY CALCUL FACTORS

### Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

| $F_a / F_r \leq e$ |    | $F_a / F_r > e$ |    |
|--------------------|----|-----------------|----|
| X                  | Y  | X               | Y  |
| 1                  | Y1 | 0.67            | Y2 |

### Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

| $X_0$ | $Y_0$ |
|-------|-------|
| 1     | Y0    |

The values for e, Y1, Y2 and Y0 are shown in the above table .

