



Main

Range of product	IID
Device short name	IID
Poles description	4P
Neutral position	Left
Network type	AC

Complementary

Device location in system	Outgoer
[In] rated current	40 A
Network frequency	50/60 Hz
[Ue] rated operational voltage	400 V EN 61008-1 AC 50/60 Hz 400/415 V IEC 61008-1 AC 50/60 Hz
Residual current tripping technology	Voltage independent
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Class AC
Rated breaking and making capacity	1500 A I _{dm} 1500 A I _m
Rated conditional short-circuit current	10 kA
Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Removable comb busbar installed
Mounting support	DIN rail
9 mm pitches	8
Width	72 mm
Connections - terminals	Tunnel terminal with flap

Environment

Standards	EN 61008-1 IEC 61008-1
RoHS EUR status	Compliant
RoHS EUR conformity date	1001

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.