

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, Strip, white, unlabeled, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, for terminal block width: 6 mm, Number of individual labels: 20, text field height: 10 mm, text field width: 6 mm

Your advantages

- The markers, which are supplied in uniform strips, can be printed onto quickly and easily using the BLUEMARK printing systems
- The UM6R-TM ... UM labeling range includes terminal markers for entrelec terminal blocks
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers support multi-line labeling

Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0830921             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | BGE21C              |
| Product key                          | BGE21C              |
| Catalog page                         | Page 174 (C-3-2019) |
| GTIN                                 | 4046356910569       |
| Weight per piece (including packing) | 1.95 g              |
| Weight per piece (excluding packing) | 1.95 g              |
| Customs tariff number                | 39269097            |
| Country of origin                    | PL                  |

# UM6R-TM (6X10) - Marker for terminal blocks



0830921

<https://www.phoenixcontact.com/gb/products/0830921>

## Technical data

### Product properties

|                     |                  |
|---------------------|------------------|
| Product type        | Terminal marking |
| Area of application | entrelec         |
| Pitch               | 6 mm             |
| Type                | high             |

### Marking

|                                     |    |
|-------------------------------------|----|
| Number of individual labels         | 20 |
| Number of individual labels per row | 10 |
| Number of marker strips             | 2  |

### Dimensions

|        |       |
|--------|-------|
| Width  | 6 mm  |
| Length | 10 mm |
| Pitch  | 6 mm  |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 6 mm  |
| Text field height | 10 mm |

### Material specifications

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| RoHS compliant                         | yes                                      |
| Color                                  | white (RAL 9010)                         |
| Material                               | PC                                       |
| Flammability rating according to UL 94 | V2                                       |
| Components                             | free from silicone, halogen, and cadmium |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Wipe resistance of inscriptions

|                                |                                                |
|--------------------------------|------------------------------------------------|
| Specification                  | IEC 61010-1:2010-06                            |
|                                | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0] | Test passed                                    |
| n-Hexane<br>[CAS No. 110-54-3] | Test passed                                    |

# UM6R-TM (6X10) - Marker for terminal blocks



0830921

<https://www.phoenixcontact.com/gb/products/0830921>

|                                                 |             |
|-------------------------------------------------|-------------|
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed |
|-------------------------------------------------|-------------|

Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |

Ambient conditions

|                                                     |                   |
|-----------------------------------------------------|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 120 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

# UM6R-TM (6X10) - Marker for terminal blocks



0830921

<https://www.phoenixcontact.com/gb/products/0830921>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000761 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# UM6R-TM (6X10) - Marker for terminal blocks



0830921  
<https://www.phoenixcontact.com/gb/products/0830921>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)