





FAG

61844

Deep groove ball bearing

Deep groove ball bearing 618, single row,
steel sheet metal cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S1	Rings dimensional stabilized up to 200°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	220 mm	Bore diameter
D	270 mm	Outside diameter
B	24 mm	Width
C _r	78,000 N	Basic dynamic load rating, radial
C _{0r}	97,000 N	Basic static load rating, radial
C _{ur}	3,650 N	Fatigue load limit, radial
n _G	3,200 1/min	Limiting speed
n _{gr}	2,320 1/min	Reference speed
≈m	2.5 kg	Weight



Mounting dimensions

$d_{a\min}$	227 mm	Minimum diameter shaft shoulder
$D_{a\max}$	263 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1.5 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1.5 mm	Minimum chamfer dimension
D_1	255 mm	Shoulder diameter outer ring
d_1	235.85 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

f_0	15.8	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed