

Rotary Hammer Brushless XGT®

HR010G

40Vmax, SDS-PLUS, 20 mm, 2.1J

Model HR010G is a 20mm SDS-PLUS combination hammer powered by 40Vmax XGT® Li-Ion battery.

Compact and lightweight design. This model is compatible with the new dust collection system DX16 attachment that can be connected for on-tool dust collection.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 1350 min ⁻¹
Impacts per Minute (IPM)	0 - 5000 min ⁻¹
Max. Drilling Diameter in Wood	26 mm
Max. Drilling Diameter in Concrete	20 mm
Max. Drilling Diameter in Steel	13 mm
Optimum Drilling Diameter Range in Concrete	3,2 - 12 mm
Impact Energy	2,1 J
Drilling diameter with TCT core bit	35 mm
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	101 dB(A)

User benefits

- Built-in LED light illuminates the work area
- Battery protection circuit protects against overloading, over-discharging and over-heating
- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing