


RS PRO 1.5 mm² Flexible Cable, 50 m Length

RS Stock No: 606-088

FEATURES

- **Annealed Copper Conductor:** Provides excellent conductivity and flexibility
- **Polyvinyl Chloride Jacket:** Offers robust protection and insulation
- **Plain Conductor Type:** Ensures consistent electrical performance
- **Five Cores:** Supports multi-functional electrical applications
- **Voltage Rating of 500 V:** Suitable for a wide range of electrical systems
- **30/0.25 Core Strands:** Enhances flexibility and ease of installation
- **White Jacket Colour:** Facilitates easy identification and aesthetic integration



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial settings. With a 1.5 mm² cross-sectional area and a length of 50 metres, it is ideal for installations requiring flexibility and durability. The cable is suitable for use in environments with temperatures ranging from -15 °C to 70 °C, ensuring performance in diverse conditions.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	1.5 mm ²
Cable Length	50 m
Core Strands	30/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	5
Outside Diameter	11.6 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------