

# Neodymium Ring Magnet datasheet

## Countersunk hole

- Neodymium iron boron 'rare earth' material
- Strongest magnet material available
- 80°C max. operating temp.
- High resistance to de-magnetisation
- Anisotropic
- N35 grade



### Product Information

Product No.	Diameter	Height*	Hole	Screw head	Weight	Pull force	Units / pack
		<i>mm</i>			<i>kg</i>		
<b>N822</b>	20	10	6 csk	M6	0.0214	4.7	1
<b>N823</b>	37	3.5	6 csk	M6	0.0275	4.9	1

\*magnetic axis