



**Part Number :** [1720631311](#)  
**Product Description :** Mega-Fit Crimp Terminal,  
Female, 0.76µm Gold (Au) Plating, 16-14 AWG, Reel  
**Series Number :** 172063  
**Status :** Active  
**Product Category :** Crimp Terminals



## Documents & Resources

### Drawings


- [1720631311\\_sd.pdf](#)
- [PK-76823-001-001.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

### Specifications

- [AS-76823-100-001.pdf](#)
- [PS-76823-100-001.pdf](#)
- [TS-76823-001-001.pdf](#)
- [TS-76823-100-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	172063
Description	Mega-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 16-14 AWG, Reel
Application	Power, Wire-to-Board
Product Name	Mega-Fit
UPC	887191559049

### Electrical

Current - Maximum per Contact	23.0A
Voltage - Maximum	600V AC (RMS)/DC

### Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Net Weight	0.328/g
Packaging Type	Reel
Plating min - Mating	0.762µm

Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.75mm (0.148")
Wire Size (AWG)	14, 16
Wire Size mm <sup>2</sup>	1.50

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

### Mates With / Use With

#### Use with Part(s)

Description	Part Number
Mega-Fit Receptacle Housing, Dual Row, 2 Circuit, Glow-Wire Capable, Bag	<u>1700010102</u>
Mega-Fit Receptacle Housing, Dual Row, 4 Circuit, Glow-Wire Capable, Bag	<u>1700010104</u>
Mega-Fit Receptacle Housing, Dual Row, 6 Circuit, Glow-Wire Capable, Bag	<u>1700010106</u>
Mega-Fit Receptacle Housing, Dual Row, 8 Circuit, Glow-Wire Capable, Bag	<u>1700010108</u>
Mega-Fit Receptacle Housing, Dual Row, 10 Circuit, Glow-Wire Capable, Bag	<u>1700010110</u>
Mega-Fit Receptacle Housing, Dual Row, 12 Circuit, Glow-Wire Capable, Bag	<u>1700010112</u>
Mega-Fit Receptacle Housing, Dual Row, 2 Circuit, UL 94 V-0, Bag	<u>1716920102</u>
Mega-Fit Receptacle Housing, Dual Row, 4 Circuit, UL 94 V-0, Bag	<u>1716920104</u>
Mega-Fit Receptacle Housing, Dual Row, 6 Circuit, UL 94 V-0, Bag	<u>1716920106</u>
Mega-Fit Receptacle Housing, Dual Row, 8 Circuit, UL 94 V-0, Bag	<u>1716920108</u>

Mega-Fit Receptacle Housing, Dual Row, 10 Circuit, UL 94 V-0, Bag	<a href="#"><u>1716920110</u></a>
Mega-Fit Receptacle Housing, Dual Row, 12 Circuit, UL 94 V-0, Bag	<a href="#"><u>1716920112</u></a>

---

## Application Tooling

### Global

Description	Part Number
Extraction Tool for Mega-Fit Crimp Terminals, 16-12 AWG	<a href="#"><u>638240810</u></a>
Hand Crimp Tool for Mega-Fit Crimp Terminals, mm <sup>2</sup> Wires	<a href="#"><u>638274900</u></a>
FineAdjust Applicator for Mega-Fit Crimp Terminals, for 16-14 AWG or 1.00mm <sup>2</sup> and 1.50mm <sup>2</sup> Wire with Insulation Diameter 2.36-3.56mm	<a href="#"><u>639023300</u></a>
Hand Crimp Tool for Mega-Fit Female Crimp Terminals, 16-12 AWG Wire	<a href="#"><u>2238631200</u></a>