


Product data sheet

Specifications



Repacked, load-shedding contactor, Acti9 CDS, 2 C, white

A9C15908W



This repacked option saves 2.613 over the standard condition

Main

range of product	Acti9
Product name	Acti9 CDS
Product or component type	Load-shedding contactor
Device short name	CDS
Number of channels	2
Control and monitoring type	Cascade
Poles description	1P

Complementary

Setting	75 45 20 90 5 10 30 60 50 40 15 25
Power consumption in VA	12 VA
[Ue] rated operational voltage	230 V AC - 15...10 % at 50/60 Hz
Rated current	15 A for non-priority circuit Adjustable from 5 to 90 A for priority circuit
Local signalling	Load-shedding indication: 2 LEDs (yellow)
Mounting support	35 mm symmetrical DIN rail Wall mounted Panel mounting
9 mm pitches	10
Connections - terminals	Non-priority circuit: screw terminal2.5...10 mm² flexible Non-priority circuit: screw terminal2.5...10 mm² rigid Priority circuit: screw terminal10...35 mm² flexible Priority circuit: screw terminal10...50 mm² rigid
IP degree of protection	IP20 conforming to IEC 60529
Height	77 mm
Width	90 mm
Depth	60 mm
Product weight	0.3 kg
Colour	White (RAL 9003)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Tightening torque	Non-priority circuit: 2 N.m Priority circuit: 3.5 N.m
Wire stripping length	12 mm 13 mm

Environment

Standards	EN 50081-1 NF C 61-750 EN 50081-2
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-40...70 °C
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	8.4 cm
Package 1 Length	10.0 cm
Package 1 Weight	298.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	8.465 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

3 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

429095ee-388a-4184-bea4-16f87e374975

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins