



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 14

Connector Product Type: Connector Assembly

Operating Voltage: 250 VDC

Connector System: Wire-to-Board, Wire-to-Panel

Sealable: No

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board, Wire-to-Panel
Sealable	No
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Number of Positions	14
Number of Power Positions	0
Number of Signal Positions	14

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	Yes
Contact Type	Socket



Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling
Mating Alignment	With
Connector Mounting Type	Panel Mount
Mating Retention	With
Panel Mount Feature	With

Housing Features

Housing Color	Black
Housing Material	PA 6.6
Circular Connector Shell Size	20

Dimensions

Assembly Length	45.11 mm[1.776 in]
-----------------	--------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	24
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 213571-2  
CPC PLUG KIT 20-14 W/O CBL CL

Also in the Series | AMP Circular Plastic Connectors

Circular Power Connectors(423)

Connector Backshells(1)

Connector Caps & Covers(16)

Connector Seals & Cavity Plugs(35)




Connector Strain Relief(60)



Insertion & Extraction Tools(1)

Customers Also Bought



TE Part #213650-1  
CPC 20-14 FREE HANGING RCPT




TE Part #5-146253-7  
14 MODII HDR DRST B/A .100CL LF




TE Part #9-1419111-4  
PT571048



TE Part #2-1418362-1  
62 POS MIXED HEADER CODB



TE Part #1744418-7  
7 POS EP 2.5 HDR, GLOW WIRE



TE Part #133041-E  
MJ DS-LG5 \* \* 8 8 4 \* GF9 \* \* 30 \* J 3 1



TE Part #5-146253-5  
10 MODII HDR DRST B/A .100CL L



TE Part #5-534998-4  
08 MODIV VRT DR CE 100/125



TE Part #6116353-1  
INV MJ,1X2,PNL GRD,LED (G/Y)



TE Part #5745395-2  
HD-20 RCPT 9P RA 318 FFSCRLK

Documents

Product Drawings

CPC PSTD RCPT ASSY SZ 20-14 LF

English

CAD Files

3D PDF

English

Customer View Model

ENG\_CVM\_1-213928-1\_C.2d\_dxf.zip



- English
- Customer View Model
- ENG\_CVM\_1-213928-1\_C.3d\_igs.zip
- English
- Customer View Model
- ENG\_CVM\_1-213928-1\_C.3d\_stp.zip
- English
- 3D PDF
- 3D
- Customer View Model
- ENG\_CVM\_CVM\_1-213928-1\_D.2d\_dxf.zip
- English
- Customer View Model
- ENG\_CVM\_CVM\_1-213928-1\_D.3d\_igs.zip
- English
- Customer View Model
- ENG\_CVM\_CVM\_1-213928-1\_D.3d\_stp.zip
- English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

CSA Certificate

English