

synchronous motor - BMP - 480 VAC - 1.5 kW - IP65 - IEC

BMP1002F3NA2A

EAN Code: 3606480564444

Main

Product or component type	Synchronous motor	
Device short name	ВМР	
Maximum mechanical speed	3600 rpm	
Nominal output power	1500 W with drive ATV32 at 1.5 kW 400 V three phase 1500 W with drive ATV320 at 1.5 kW 400 V three phase	
Nominal torque	4.77 N.m with drive ATV32 at 1.5 kW 400 V three phase 4.77 N.m with drive ATV320 at 1.5 kW 400 V three phase	
Nominal speed	3000 rpm with drive ATV32 at 1.5 kW 400 V three phase 3000 rpm with drive ATV320 at 1.5 kW 400 V three phase	
Product compatibility	Variable speed drive ATV32 at 1.5 kW 400 V three phase Variable speed drive ATV320 at 1.5 kW 380500 V three phase	
Shaft end	Keyed	
IP degree of protection	IP65 standard IP67 with IP67 kit	
Holding brake	Without	
Mounting support	International standard flange	
Electrical connection	Rotatable right-angled connector	

Complementary

Range compatibility	Altivar Machine ATV320 Altivar 32	
[Us] rated supply voltage	480 V	
Network number of phases	Three phase	
Maximum current Irms	6.2 A with drive ATV32 at 1.5 kW 400 V three phase 6.2 A with drive ATV320 at 1.5 kW 400 V three phase	
Nominal operating frequency	250 Hz with drive ATV32 at 1.5 kW 400 V three phase 250 Hz with drive ATV320 at 1.5 kW 400 V three phase	
Minimum operating frequency	25 Hz with drive ATV32 at 1.5 kW 400 V three phase 25 Hz with drive ATV320 at 1.5 kW 400 V three phase	
Maximum operating frequency	300 Hz with drive ATV32 at 1.5 kW 400 V three phase 300 Hz with drive ATV320 at 1.5 kW 400 V three phase	
Shaft diameter	19 mm	
Shaft length	40 mm	
key width	6 mm	
Motor flange size	100 mm	
Torque constant	1.56 N.m/A at 40 °C	

Number of motor poles	5
Number of motor stacks	2
Rotor inertia	6.28 kg.cm ²
Stator resistance	1.75 Ohm at 40 °C
Stator inductance	7.65 mH for q-axis winding at 40 °C 6.64 mH for d-axis winding at 40 °C
Maximum radial force Fr	990 N at 1000 rpm 790 N at 2000 rpm 690 N at 3000 rpm 620 N at 4000 rpm
Maximum axial force Fa	0.2 x Fr
type of cooling	Natural convection
Length	160.6 mm
Centring collar diameter	95 mm
centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	9 mm
Circle diameter of the mounting holes	115 mm
Net weight	4.92 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.000 cm
Package 1 Width	22.400 cm
Package 1 Length	40.900 cm
Package 1 Weight	5.904 kg
Unit Type of Package 2	P06
Number of Units in Package 2	6
Package 2 Height	77.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	44.380 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	2aa8eec9-ed15-418c-9f66-488c5df8d4dd
REACh Regulation	REACh Declaration
PVC free	Yes

Use Again


○ Repack and remanufacture	
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings


Dimensions



Parallel Key According to DIN 6885 A



Female Thread of Shaft According to DIN 332-D




L	mm	160.6
	in.	6.32
В	mm	40
	in.	1.57
	mm	19

Product datasheet BMP1002F3NA2A

	in.	0.75
D	mm	6
	in.	0.24
E	mm	21.5
Ц	in.	0.85
F	mm	30
L	in.	1.18
G	mm	5
9	in.	0.20
Н		M6
N	mm	2.8
IN	in.	0.11
0	mm	5
0	in.	0.20
Р	mm	16
Г	in.	0.63
Q	mm	21
γ	in.	0.83
s	mm	6.4
5	in.	0.25
Т	mm	5
	in.	0.20

Performance Curves

Performance curves



- M: Torque in Nm
- n: Speed in rpm
- f: frequency in Hz
- 1: Only permissible during acceleration and deceleration phases.
- 2: Continuous operation with the default values from the configuration file.