

Product data sheet

Specifications



Repacked Data socket, New Unica, RJ45 CAT 6A, STP, straight, click, shuttered, 2 module, white

NU344918W



This repacked option saves 0.547 over the standard condition

Main

Range	New Unica
Product or component type	Data socket
Device application	Communication
Device presentation	Mechanism
Colour tint	White (RAL 9003)
Data socket type	RJ45 8 contact(s) Cat.6A < 500 MHz
Provided equipment	Protective flap Label holder

Complementary

Communication network type	10GBASE-T
Communication port protocol	ATM 1200 Mbps
Number of modules	2 modules
Socket number	1
Type of footprint	Infraplus
Connector type	S-One
Cable shielding type	S/FTP
Organization of wire	Shielded twisted pair
Connections - terminals	Click
Device mounting	Flush
Fixing mode	Clip-in
Installation direction	Straight
Material	Thermoplastic ABS-UV stabilised: central plate
Quantity per set	1
Depth	40.5 mm
Width	45 mm
Height	45 mm
Embedding depth	40.5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
-------------------------------	---

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-5...35 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	7.500 cm
Package 1 Length	9.000 cm
Package 1 Weight	46.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.110 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.5 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

89f48f58-8743-4a8c-aad2-c796c3e70cb3

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Wiring diagram

