

FEATURES

- **Sintered Bronze Material:** Provides high durability and wear resistance, ensuring long service life.
- **Flanged Design:** Facilitates easy installation and secure positioning in applications.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads effectively.
- **Bore Size of 1.25 in:** Compatible with a wide range of shafts for versatile use.

RS PRO 1.25 in Plain Bearing, Flanged

RS Stock No: 518-167



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

This RS PRO plain bearing is designed for reliable performance in various industrial applications. Constructed from sintered bronze, it offers excellent durability and resistance to wear. The flanged design ensures easy installation and secure positioning, making it ideal for use in machinery where precise alignment is crucial.

General Specifications

Bore Size	1.25 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	1.5 in
Width	3/4 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

