

Industrial Labeling ~ K5100

- [K5100 Features](#)
- [K5100 Printing Specs](#)
- [K5100 Media Specs](#)
- [K5100 Physical Specs](#)
- [K5100 Electrical Specs](#)
- [K5100 Environmental Specs](#)
- [K5100 Limited Warranty](#)
- [Getting Started with the K5100](#)
- [K5100 Accessories](#)
- [K5100 Cartridge Supplies](#)



K5100 Series Features:

- Supply is easy loading.
- Print graphics, logos, bar codes, and data records.
- Internal battery charger.
- Use as stand alone or connected to PC.
- Compatible with Win95/98/2000/XP.
- Comes with Kroy Label Designer Software(KLDS) and drivers.
- Uses continuous and die cut media.
- Built in cutter and feed control.
- Audible key clicks.
- Flash upgradeable firmware.
- Real time clock with time/date stamping ability.
- Alpha/Numeric sequencing (A-Z, 1-999).

K5100 Series Printing Specifications:

- Thermal transfer and direct thermal printing
- Auto sizing text features.
- Built in cutter and feed control

- Two line x 16 Character LCD display.
- 6-72 Point w/ downloadable and scaleable fonts.
- 10 resident bar codes including Code 39 and 128.
- On Board memory to store formats and fonts.
- Print speeds vary by content up to 2" per second
- 300 dots per inch (12 dots per mm)
- Maximum print width: .97" (24.7mm)
- Maximum label width: 1" (25.4mm)
- Maximum label length: 20" (508mm)

K5100 Series Media Specifications:

- Tape supply widths: .5", .8", 1"
- Tape supply length: 40 feet (12.2m)
- Shrink Tube supply length: 110" (2.8m)
- Media type: Self-laminating wire wraps, polyolefin shrink tubing, polyester industrial labels, laminated labels, tamper evident labels, cast vinyl labels, component and terminal block die cut labels
- All supplies are housed in a self-contained cartridge for rapid supply change

K5100 Series Physical Specifications:

- Printer: 11.0" L x 6.0" W x 4.0" H

K5100 Series Electrical Specifications:

- Battery operated or AC Adapter.
- Optional batteries - "C"-size rechargeable 2500mAh Ni-Cad
- AC adapter version: Output: 12VDC, UL Listed, C-UL, CE Recognized
- Meets VDE-B and FCC Part 15 class B RFI limits
- RS 232 Serial port, 9600 - 115,200 baud.

K5100 Series Environmental Specifications:

- Operating temperature: 45 F to 105 F (7 C to 40 C)
- Supply cartridge storage temperature: - 60 F to 105 F (15 C to 40 C) shelf life is reduced at higher temperatures - damage may occur at temperatures as high as 120 F (50 C)
- Operating /storage humidity limit: 90% RH non-condensing

K5100 Series Limited Warranty:

- 1 year parts and labor
- 90 day printhead and software

Getting Started with the K5100 Series Labeling System

Part Number	Description
2561000	K5100 Handheld Industrial Printer With 110V AC Adapter Serial Cable KLDS Software

K5100 Accessories

Part Number	Description
2563900	K5100 Carrying Case Also will fit the K2500 Series Printers

K5100 Cartridge Supplies:

- [**.375 Labeling Supplies**](#)
- [**.50" Labeling Supplies**](#)
- [**.80" Labeling Supplies**](#)
- [**1.0" Labeling Supplies**](#)
- [**1.0" Laminated Labeling Supplies**](#)
- [**1.0" Cast Vinyl Supplies**](#)
- [**Self Laminating Wire Wraps**](#)
- [**Shrink Tube**](#)
- [**Die Cut Polyester Labeling Supplies**](#)
- [**Tamper Evident Labeling Supplies**](#)

Take advantage our our [**Extended Warranty**](#) Program
