

Product datasheet


Specifications



Thalassa PHD outdoor heavy duty - enclosure H2093 W750 D420 IP55 plain door

Local distributor code:
402657653

NSYPHDZT2074P

 **Discontinued on:** 9 Feb 2023

 **Discontinued**

EAN Code: 3606480676130

Main

Range	Thalassa
Product	Thalassa PHD
Application	Outdoor heavy duty
Certification	UL conforming to UL 508 A 2007 Bureau Veritas conforming to IEC 61969-3 2011 Bureau Veritas conforming to IEC 61439-5 2010 DEKRA conforming to IEC 62208 2011
Enclosure type	Multi-purpose
Category	Suitable enclosure
Version	PHDZT
Enclosure height with canopy	2093 mm
Canopy height	38 mm
Enclosure width	750 mm
Enclosure depth	420 mm
Enclosure mounting	Floor-standing
Device composition	1 body in polyester double reinforced with fibreglass 2 doors in polyester double reinforced with fibreglass in one above the other 1 document pocket in plastic A4 format 1 cable gland plate in aluminium 1 canopy in polyester reinforced with fibreglass 2 door retainer in steel with anti-corrosive coating

Complementary

Body type	Sealed assembled body
Door type	Plain
Number of doors	2 door(s)
Door opening side	Right or left (120 °)
Lock type	4 points lock, handle with 1242E key lock and padlock door
Accessibility for operation	Front Bottom
Maximum lifting load	500 kg
Removable parts	Door by hinges Canopy by fixing element Cable gland plate by fixing element
Material	Polyester double reinforced with fibreglass
Colour	Grey (RAL 7035)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 508 A IEC 61439-5 IEC 62208 IEC 61969-3
Electrical insulation class	Class II conforming to IEC 61439-1 2011

Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262 (plain door)
Mechanical robustness	Vandal-proof conforming to EN/IEC 61439-5 version 2010
Fire resistance	960 °C conforming to IEC 62208
Ambient air temperature for operation	-45...80 °C conforming to IEC 61969-3 class 1
Ambient air temperature for storage	-25...40 °C
Corrosion withstand	90...100 % conforming to ISO 12944 C4H
Environmental withstand	Solar radiation: class 1 up to 1120 W/m² conforming to IEC 61969-3:2011 Surrounding air withstand: class 1 up to 180 km/h conforming to IEC 61969-3:2011 Ultraviolet degradation test: class 1 conforming to ISO 4892-2:2013 Formation of ice and frost: class 1 conforming to IEC 61969-3:2011 Fauna and flora withstand: class 1 conforming to IEC 61969-3:2011 : class 1 conforming to IEC 61969-3:2011
Thermal management options	Fan: 1500 W for a maximum noise level of 60 dB With external cooling 4000 W Natural: 1008 W at -25 °C Natural: 441 W at 20 °C Natural: 189 W at 40 °C According to cooling architecture 1500 W

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	216.000 cm
Package 1 Width	80.000 cm
Package 1 Length	50.000 cm
Package 1 Weight	78.800 kg

Logistical informations

Country of origin	ES
-------------------	----

Contractual warranty


Warranty	18 months
----------	-----------

Environmental Data


Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)


[How we assess product sustainability >](#)

 Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	613
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	1341ad4e-77b9-40e3-bab0-32043fbc5959

Use Again

 Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No