

# Product datasheet

Specifications



## Multi9 - C60N - MCB - 4P - 50 A - B Curve - 415 V - 10 kA

M9F10450

EAN Code: 3606480929236

### Main

Range	Multi9
Product name	Multi9 C60
Product or component type	Miniature circuit-breaker
Device short name	C60N
Device application	Distribution
Poles description	4P
Number of protected poles	4
[In] rated current	50 A at 50 °C conforming to EN/IEC 60947-2
Network type	DC AC
Network frequency	50/60 Hz
Trip unit technology	Thermal-magnetic
Curve code	B
Breaking capacity	40 kA Icu at <= 250 V DC conforming to EN/IEC 60947-2 10 kA Icu at 415 V AC 50/60 Hz between phases conforming to EN/IEC 60947-2 20 kA Icu at 240 V AC 50/60 Hz between phases conforming to EN/IEC 60947-2 6 kA Icu at 440 V AC 50/60 Hz between phases conforming to EN/IEC 60947-2
Utilisation category	Category A conforming to EN/IEC 60947-2
Standards	EN/IEC 60947-2
Product certifications	EAC CCC
Quality labels	UKCA RCM

### Complementary

[Ue] rated operational voltage	240 V AC 50/60 Hz between phases 415 V AC 50/60 Hz between phases 440 V AC 50/60 Hz between phases <= 250 V DC
Magnetic tripping limit	4 x In +/- 20 % AC 5.7 x In +/- 20 % DC
[Ics] rated service breaking capacity	7.5 kA 75 % conforming to EN/IEC 60947-2 - 415 V AC 50/60 Hz 16 kA 75 % conforming to EN/IEC 60947-2 - 240 V AC 50/60 Hz 4.5 kA 75 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 40 kA 100 % conforming to EN/IEC 60947-2 - <= 250 V DC
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2

Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	81 mm
Width	72 mm
Depth	72 mm
Net weight	0.48 kg
Colour	Grey
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Tunnel type terminal (top or bottom)1.5...35 mm <sup>2</sup> - rigid Tunnel type terminal (top or bottom)1.5...35 mm <sup>2</sup> - flexible Tunnel type terminal (top or bottom)1.5...35 mm <sup>2</sup> - flexible with ferrule
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom
Earth-leakage protection	Separate block

## Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Overvoltage category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-30...70 °C
Ambient air temperature for storage	-40...80 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.2 cm
Package 1 Length	8.5 cm
Package 1 Weight	478 g
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	7.8 cm
Package 2 Width	8.9 cm

---

Package 2 Length	22.5 cm
Package 2 Weight	1.476 kg
Unit Type of Package 3	S03
Number of Units in Package 3	36
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	18.293 kg

## Logistical informations

---

Country of origin FR

## Contractual warranty

---

Warranty (in months) 18



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint 82

Environmental Disclosure [Product Environmental Profile](#)

## Use Better



### Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant

SCIP Number 40a4e715-7fff-45ff-88bf-38212f6a80a5

REACH Regulation [REACH Declaration](#)

## Use Longer



### Lifetime extension

Repair No

## Use Again



### Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No

WEEE Label  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

---

