


Features

- The characteristics correspond to the IEC 60115-1 standard specification
- General-purpose lead-type resistors
- Automatic insertion is applicable
- Availability of various types and excellent long-time stability
- Wide resistance ranges from $0.1\ \Omega$ to $10\ M\Omega$

RS PRO Carbon Film Leaded Resistor

RS Stock No.:

0327922, 0327924, 0327925, 0327927, 0327928, 0327929, 0327930, 0327931, 0327933, 0327934, 0327935, 0327937, 0327938, 0327940, 0327941




RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Applications Include:

- Telecommunications
- Medical Equipment

Construction




①	Ceramic Rod	④	Non-flame Paint With Sol Vent-proof
②	Tinned Iron Caps	⑤	Color Code
③	Carbon Film	⑥	Lead Wire


Unit: mm

Type	RS Article	L	D	H	d	Weight (g) (1000 pcs)
RSPCFR0318	0327922 0327929 0327931 0327934	3.4±0.5	1.8±0.3	29±3.0	0.41~0.48	92
RSPCFR0932	0327924 0327925 0327927 0327928 0327930 0327933 0327935 0327937 0327938 0327940 0327941	9.0±0.5	3.2±0.5	26±3.0	0.58~0.68	352

Derating Curve



Hot-Spot Temperature



Part Number Make Up

RSPCFR	0318	J	T	-	W	1001
Product Type	Dimensions (LxD)	Resistance Tolerance	Packaging Code	TCR (PPM/°C)	Power Rating	Resistance
	0318: 3.4x1.8 0932: 9.0x3.2	J: ±5%	A: Ammo B: Bulk T: Taping Reel	-:No specified	U: 1/2W W: 1/8W	R500: 0.5Ω 0010: 1Ω 1000: 100Ω 2201: 2200Ω 1001: 1KΩ 1004: 1MΩ

Electrical Specifications

Type	Power Rating at 70°C	Operating Temp. Range	Max. Working Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Resistance Range	
						±5%	
						E6	E24
0318	1/8W	-55 ~ +155°C	150V	300V	300V	0.1Ω - 0.68Ω	1Ω - 10MΩ
0932	1/2W		350V	700V	700V	0.1Ω - 0.68Ω	1Ω - 10MΩ

High Power Rating Electrical Specifications

Type	Power Rating at 70°C	Operating Temp. Range	Max. Working Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Resistance Range	
						±5%	
						E6	E24
0318	1/4W	-55 ~ +155°C	200V	400V	400V	0.1Ω - 0.68Ω	1Ω - 10MΩ
0932	1W		400V	800V	800V	0.1Ω - 0.68Ω	1Ω - 10MΩ

Operating Voltage= $\sqrt{(P \cdot R)}$ or Max. operating voltage listed above, whichever is lower.

Overload Voltage= $2.5 \cdot \sqrt{(P \cdot R)}$ or Max. overload voltage listed above, whichever is lower

█ Resistor body color:

Standard power rating: Light Brown

High power rating 0318 size: Light Brown is available only other sizes: Light Brown or Pink are available.

Please specify which color is acceptable else the light brown is a top priority.

█ For resistance value out of above range is by request. Below 10Ω are using alloy film.

Environmental Specifications

Item	Requirement	Test Method
Resistance Value	1Ω ~ 10MΩ	IEC-60115-1 4.5 Measure at a distance of 10mm from the cap end
Short Time Overload	±(0.75%+0.05Ω)	IEC-60115-1 4.13 2.5 times RCWV for 5 seconds
Insulation Resistance	>1000MΩ	IEC-60115-1 4.6 The measure was executed by V-Block methods
Endurance	±(3%+0.05Ω)	IEC-60115-1 4.25 70±2°C, RCWV (or Umax., whichever less) for 1000 hrs with 1.5 hrs "ON" and 0.5 hrs "OFF"
Damp Heat, Steady State	<100KΩ±3% >101KΩ±5%	IEC-60115-1 4.24 40±2°C, 90~95% R.H. for 56 days, loaded with 0.1 times RCWV (or Umax., whichever less)
Solderability	95% min. Coverage	IEC-60115-1 4.17 245±5°C for 3±0.5 seconds

Voltage Proof	By Type	IEC-60115-1 4.7 In V-Block for 60 seconds
Temperature Coefficient	1145/1550: < 1Ω ±1500ppmm 1Ω~100KΩ ±350ppm 100KΩ~1MΩ -0ppm-500ppm 1MΩ~ 10MΩ -0ppm-1000ppm Other sizes: < 1Ω ±1500ppmm 1Ω~100KΩ +350ppm-500 ppm 100KΩ~1MΩ -0ppm-700ppm 1MΩ~ 10MΩ -0ppm-1500ppm	IEC-60115-1 4.8 Resistance value at room temperature and room Temperature+100°C
Periodic-Pulse Overload Test	±(1%+0.05Ω)	IEC-60115-1 4.39 4 times RCWV (or Umax., whichever less) for 10000 cycles with 1 second "ON" and 25 seconds "OFF"
Solvent Resistance of Marking	No obvious deterioration of coatings and markings	IEC-60115-1 4.30 IPA for 5±0.5 min. with ultrasonic
Robustness of Terminations	Tensile: ≥ 2.5 kg(24.5N)	IEC-60115-1 4.16 Direct Load for 10 seconds In the direction off the terminal leads
Temperature Cycling	±(1%+0.05Ω)	IEC-60115-1 4.19 -55°C/155°C with 5 cycles the duration at each temperature 30 min
Resistance to Soldering Heat	±(1%+0.05Ω)	IEC-60115-1 4.18 The solder iron heated to 260°C ±5°C and applied to the termination for duration of 10±1 seconds.


RCWV(Rated continuous working voltage)= $\sqrt{P \times R}$ or Max. Operating voltage whichever is lower

■ Storage Temperature:25±10°C; Humidity < 80%RH


Taping/Packing Specification

1. Standard Type (Reel & Ammo)

Packing Methods



Reel Packing




Carbon Film Leaded Resistors

RS PRO

Type	Packing Methods			Reel Packing	
	A	B1-B2 Max	S	Across Flange (A)	Qty
0318	52+1/-0	1.2	5±0.3	72	5,000
	26+0.5/-0	1.0			
0932	52+1/-0	1.2	5±0.3	72	2,500


Ammo Packing



Unit: mm

Type	Packing Methods			Ammo Packing			
	A	B1-B2 Max	S	A	B	C	Qty
0318	52+1/-0	1.2	5±0.3	79±2	73±3	257±5	5,000
	26+0.5/-0	1.0		52±2	74±3	252±5	
0932	52+1/-0	1.2	5±0.3	79±2	58±3	257±5	1,000

Marking & Resistance Tolerance



$\pm 5\%$	E-24	1.0	1.1	1.2	1.3	1.5	1.6	1.8	2.0	2.2	2.4	2.7	3.0	3.3	3.6	3.9	4.3	4.7	5.1	5.6	6.2	6.8	7.5	8.2	9.1
	E6		1.0			1.5				2.2				3.3			4.7			6.2			6.8		

Cold	Digit	Multiplier	Tolerance	
Without	-	-	-	-
Silver	-	10^{-2}	-	-
Gold	-	10^{-1}	$\pm 5.0\%$	J
Black	0	10^0	-	-
Brown	1	10^1	-	-
Red	2	10^2	-	-
Orange	3	10^3	-	-
Yellow	4	10^4	-	-
Green	5	10^5	-	-
Blue	6	10^6	-	-
Violet	7	10^7	-	-
Grey	8	10^8	-	-
White	9	10^9	-	-