

Features

- Neoprene Rubber
- Black
- Flexible & durable
- Resistant to ozone, sunlight and atmospheric ageing
- Flammability rating UL 94 HF-1

RS PRO Black Rubber Sheet,

1m x 2m x 1.5mm

RS Stock No.: 733-6753



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Introducing a series of neoprene rubber sponge sheets from RS PRO. These black neoprene rubber sheets are suitable for use, both indoor & outdoor, offer moderate resistance to atmospheric ageing, sunlight, oils, and greases.

RS PRO Rubber Sheet Options

- 1 m x 2 m x 1.5mm - RS Stock no: 733-6753
- 1 m x 2 m x 1.5mm - RS Stock no: 733-6731
- 1 m x 2 m x 3mm - RS Stock no: 733-6757
- 1 m x 2 m x 16mm – RS Stock no: 733-6741
- 1 m x 2 m x 3mm - RS Stock no: 733-6735
- 1 m x 2 m x 6mm - RS Stock no: 733-6744
- 1 m x 2 m x 6mm - RS Stock no: 733-6766
- 1 m x 2 m x 10mm - RS Stock no: 733-6747
- 1 m x 2 m x 10mm - RS Stock no: 733-6769
- 1 m x 2 m x 20mm - RS Stock no: 733-6750
- 1 m x 2 m x 25mm - RS Stock no: 103-4059

General Specifications

Colour	Black
Density	1.22 g/cm ³
Adhesive Backing	Yes
Suitability	Animal Oil, Cold Water, Dilute Acid, Dilute Alkali, Ethylene Glycol, Fuel, Hot Water, Vegetable Oilimal Oil; Cold Water; Dilute Acid; Dilute Alkali;
Elongation	>180%
Water Absorption	0.8
Compression Set (50% 22h 20°C)	19.10%
Resistance to Air+UV	Excellent
Resistance to Oil	Poor
Resistance to Acids	Good
Environmental Protection	CFC and HFC FREE / CAN BE RECYCLED
Application	Sound-proofing, Noise and Heat insulation

Mechanical Specifications

Length	1000mm
Thickness	1.5mm
Width	2m
Tensile Strength	500 KN/m ²

Operation Environment Specifications

Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C

Approvals

Flammability Rating	FMVSS 302; UL94 HBF, ASTM D1056-00, AFNOR 99-211
---------------------	--

Similar Products

Parameters	Stock#	Stock#	Stock#	Stock#
Brand	RS PRO	RS PRO	RS PRO	RS PRO
Colour				
Density				
Adhesive Backing				
Suitability				
Elongation				
Water Absorption				
Hardness				
Finish				
Durometer				
Density (Gram/Cm ₃)				
Skin- skin/skin (mm)				
Compression Set (50% 22h 20°C)				
Water absorption, max. change in weight (%)				
Resistance to Air+UV				
Resistance to Oil				
Resistance to Acids				
Environmental Protection				
Cutting				

STANDARD ACCESSORIES