

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box



1335178

<https://www.phoenixcontact.com/in/products/1335178>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Splice box, design: Rail-mountable module, degree of protection: IP20, material: Metal, connection method: Splicing, color: gray, Ethernet

Product description

FDX 20 series DIN rail splice box, assembled with 6x E2000® duplex coupling, fully assembled and ready for splicing with pre-assembled 900 µm pigtails (OM1 UPC). Splice holder, for separately available shrink and crimp splicing protection, on a patented splice comb made from powder-coated sheet steel. Cable insertion possible via cable gland from above or below. Housing, 2-part, prepared for DIN rail mounting through the rear-side adapter. The adapter can also be mounted on the side.

Scope of supply:

DIN rail housing with integrated splice comb (mounted), assembled with 6x E2000® duplex coupling, 12x pigtail (OS2 APC), 1x splice holder, 1x cable gland (M20x1.5)

Your advantages

- Intuitive front-panel operation and clear control cabinet layout thanks to uniform design
- Flexible DIN rail mounting possible in six positioning directions
- Suitable for industrial applications
- Reduced installation time with plug-and-play
- Pin assignment straight in line in a link
- Continuously reliable data connection, thanks to extensively tested components
- Snap-on mounting on standard DIN rails NS 35/7.5 or NS 35/15
- Transmission rate up to 1000 Mbps

Commercial data

Item number	1335178
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	*****
Product key	ABNGAA
GTIN	4063151633868
Weight per piece (including packing)	804 g
Weight per piece (excluding packing)	667.716 g
Customs tariff number	85367000
Country of origin	DE

Technical data

Notes

Order information:

In addition, shrink splice protection (Item No.: 1019676) or crimp splice protection (Item No.: 1019678) must be ordered separately.

Product properties

Product type	Network distributor box
Type	Rail-mountable module
Sensor type	Ethernet
No. of cable outlets	2
Number of slots	12

Electrical properties

Transmission medium	FO
---------------------	----

Connection data

Connection technology

Connection method	Splicing
-------------------	----------

Material specifications

Color	gray
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	Powder-coated, gray

Cable/line

Cable type	Multimode fiberglass
Cable type	900 µm
Cable structure	semi-loose compact wires (STB)
External cable diameter	≤ 12.00 mm (of 6 mm) 6 mm ... 12 mm
Wire diameter incl. insulation	900 µm
Halogen-free	yes
Resistance to oil	no
Flame resistance	yes

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box



1335178

<https://www.phoenixcontact.com/in/products/1335178>

Ambient conditions

Degree of protection	IP20 (according to IEC 60529)
	IP20
Ambient temperature (operation)	-25 °C ... 70 °C ()
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Resistance to oil	no

Standards and regulations

Flame resistance	yes
Resistance to oil	no

Mounting

Mounting type	DIN rail mounting
Assembly note	Option for flexible replugging of DIN rail adapter

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box



1335178

<https://www.phoenixcontact.com/in/products/1335178>

Classifications

ECLASS

ECLASS-11.0	19170113
ECLASS-12.0	19170113
ECLASS-13.0	19170113

ETIM

ETIM 9.0	EC001130
----------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b10df1c9-83b2-41f8-bfb7-5637879a65a4

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box



1335178

<https://www.phoenixcontact.com/in/products/1335178>

Mandatory accessories

FOC-SHRINKSPLICE-PROTECT - Shrink splice protection

1019676

<https://www.phoenixcontact.com/in/products/1019676>



Shrink splice protection, design: Straight, degree of protection: IP20, cable outlet: above and below, color: transparent

FOC-CRIMPSPLICE-PROTECT - Crimp splice protection

1019678

<https://www.phoenixcontact.com/in/products/1019678>



Crimp splice protection, design: Straight, degree of protection: IP20, connection method: Crimp connection, cable outlet: above and below, color: Bare metallic

Accessories

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box

1335178

<https://www.phoenixcontact.com/in/products/1335178>



FOC-OE-OE-GL-U-OM1-12/... - FO cable

1286223

<https://www.phoenixcontact.com/in/products/1286223>




GOF universal cable, 12-wire, loose tube cable for fixed installation, non-metallic rodent protection, can be easily stripped, UV-resistant, high mechanical and thermal stability, low smoke, halogen-free and self-extinguishing, improved tread resistance, longitudinally and transversely watertight

FOC-TOOL-FERRULECLEANER-2.50 - FO accessories

1407029

<https://www.phoenixcontact.com/in/products/1407029>



2.50 mm ferrule cleaner, for ST, SC, FC, E2000 (also APC), approx. 500 cleaning cycles

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box

1335178

<https://www.phoenixcontact.com/in/products/1335178>



FOC-TOOL-STICKCLEANER-2.50 - FO accessories

1407002

<https://www.phoenixcontact.com/in/products/1407002>



Stick cleaner for couplings and plug end faces, 2.50 mm (ST, SC), Pcs. / Pkt.: 10

A-INSP-M20-68N-P-LG - Screw plug

1424519

<https://www.phoenixcontact.com/in/products/1424519>



Screw plug, material for screw connection: PA, connecting thread: M20 x 1.5, color: lightgray RAL 7035, with O-ring

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box



1335178

<https://www.phoenixcontact.com/in/products/1335178>

WP-CN PA M20 - Counter nut

3241134

<https://www.phoenixcontact.com/in/products/3241134>

Counter nut, for threads M20, color: gray



SF-PH 1-80 - Screwdriver

1212559

<https://www.phoenixcontact.com/in/products/1212559>

Screwdriver, PH crosshead (lasered), uninsulated, size: PH 1 x 80, 2-component grip, with non-slip grip



FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box

1335178

<https://www.phoenixcontact.com/in/products/1335178>



SF-SL 1,0X5,5-150 - Screwdriver

1212552

<https://www.phoenixcontact.com/in/products/1212552>




Screwdriver, bladed (lasered), size: 1.0 x 5.5 x 150 mm, 2-component grip, with non-slip grip

E/NS 35 N - End bracket

0800886

<https://www.phoenixcontact.com/in/products/0800886>



End clamp, width: 9.5 mm, color: gray

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box

1335178

<https://www.phoenixcontact.com/in/products/1335178>



NBC-PP-G1PGY - DIN rail adapter

1041740

<https://www.phoenixcontact.com/in/products/1041740>



DIN rail adapter, design: Headers with shielding, degree of protection: IP20, material: PC-GF10, connection method: Quick connection, without assembled modules

FL DIN RA - DIN rail adapter

2891053

<https://www.phoenixcontact.com/in/products/2891053>



The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box



1335178

<https://www.phoenixcontact.com/in/products/1335178>

G-INS-M20-S68N-PNES-GY - Cable gland

1411125

<https://www.phoenixcontact.com/in/products/1411125>



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 6 mm ... 12 mm, shielding: no, connecting thread: M20 x 1.5, color: silver-gray RAL 7001

TML (104X10)R - Marker strip

0801835

<https://www.phoenixcontact.com/in/products/0801835>



Marker strip, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, for terminal block width: 104 mm, Number of individual labels: 1500, text field height: 10 mm, text field width: 104 mm

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box



1335178

<https://www.phoenixcontact.com/in/products/1335178>

TML (EX9,5)R TR - Marker strip

0816634

<https://www.phoenixcontact.com/in/products/0816634>



Marker strip, Roll, transparent, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: adhesive, for terminal block width: 30000 mm, Number of individual labels: 1, text field height: 9.5 mm, text field width: 40000 mm

EMLS (70X32)R SR - Safety label with special adhesive

0800346

<https://www.phoenixcontact.com/in/products/0800346>



Safety label with special adhesive, Roll, silver, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 500, text field height: 32 mm, text field width: 70 mm

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box



1335178

<https://www.phoenixcontact.com/in/products/1335178>

EML-HA (76X51)R - Label for rough surfaces

0830609

<https://www.phoenixcontact.com/in/products/0830609>



Label for rough surfaces, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 1000, text field height: 51 mm, text field width: 76 mm

PML-W100 (25X25)R - Warning label

0830429

<https://www.phoenixcontact.com/in/products/0830429>



Warning label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, diameter: 0 mm, Number of individual labels: 500, text field height: 25 mm, text field width: 25 mm

FOC-FDX20-PP-E2D6-OM1-PT9 - Splice box



1335178

<https://www.phoenixcontact.com/in/products/1335178>

LS-EMLP (60X15) WH - Device marker

0831696

<https://www.phoenixcontact.com/in/products/0831696>

Device marker, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 20, text field height: 15 mm, text field width: 60 mm



WML-RFID/HF 14 (25X19)R - Cable marker

0803386

<https://www.phoenixcontact.com/in/products/0803386>



Cable marker label with RFID-HF transponder, roll, white, unmarked, can be printed with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X1.2, mounting type: adhesive, min. cable diameter: 9 mm, max. cable diameter: 14 mm, lettering field size: 25 x 19 mm

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in