

# Product datasheet

Specifications



Kit for heavy load. Kit composed with 2 brackets. Maximum load 400 kg

NSYAEPPFS3DW80

EAN Code: 3606480323034

## Main

Range	PanelSeT
Accessory / separate part category	Fixing accessory
Product or component type	Wall fixing support
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting location	Top and bottom, on rear of the enclosure
Range compatibility	PanelSeT
Device composition	fixing screws 2 lug 2 pre-mounted sealing gasket
Quantity per set	Set of 1

## Complementary

Material	Steel
Fixing mode	Screwed - screw type M8 - inside location
Permanent permissible load	350 kg
Height	Fixing centers: 47 mm
Width	800 mm
Depth	Wall-enclosure separation : 7.5 mm
Net weight	2.632 kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	80.000 cm
Package 1 Width	8.000 cm
Package 1 Length	2.500 cm
Package 1 Weight	2.554 kg
Unit Type of Package 2	P12
Number of Units in Package 2	20
Package 2 Height	40.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm

---

Package 2 Weight	84.500 kg
------------------	-----------

## Logistical informations

---

Country of origin	FR
-------------------	----

## Contractual warranty

---

Warranty (in months)	18
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

## Use Better



### Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

End of life manual availability

No need of specific recycling operations

Take-back

No