

Productname : ZINC PRIMER      Creationdate : 15.06.20 Version : 2.3  
Ref.Nr.: BDS000189\_3\_20200615 (EN)      Replaces: BDS000189\_20181010

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

ZINC PRIMER  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Paints

### 1.3. Details of the supplier of the safety data sheet

CRC Industries Europe BV  
Touwslagerstraat 1  
9240 Zele  
Belgium  
Tel.: +32(0)52/45.60.11  
Fax.: +32(0)52/45.00.34  
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Smedsgatan 3-5 LT4, PL62, 08101 LOJO	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

### 1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1  
Extremely flammable aerosol.  
Pressurised container: May burst if heated.

Classification is based on test data.



<b>Productname :</b>	ZINC PRIMER	<b>Creationdate :</b>	15.06.20 Version : 2.3
<b>Ref.Nr.:</b>	BDS000189_3_20200615 (EN)	<b>Replaces:</b>	BDS000189_20181010

**Health:** Skin irritation, category 2  
Causes skin irritation.  
Eye irritation, category 2  
Causes serious eye irritation.

Classification based on calculation method.

**Environment:** Hazardous to the aquatic environment, chronic category 3  
Harmful to aquatic life with long lasting effects.

Classification based on calculation method.

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

**Hazard pictogram(s):**



<b>Signal word:</b>	Danger
<b>Hazard statement(s):</b>	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H315 : Causes skin irritation. H319 : Causes serious eye irritation. H412 : Harmful to aquatic life with long lasting effects.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P280 : Wear protective gloves/protective clothing/eye protection/face protection. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.
<b>Supplemental Hazard information:</b>	Contains: 2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime May produce an allergic reaction.

**Dir. 2004/42/EC on the limitation of emissions of volatile organic compounds (VOC) of organic solvents in certain paints and varnishes and vehicle refinishing products** Cat.II B (e) - VOC max. 840 g/l

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.



**Productname :** ZINC PRIMER  
**Ref.Nr.:** BDS000189\_3\_20200615 (EN)  
**Creationdate :** 15.06.20 Version : 2.3  
**Replaces:** BDS000189\_20181010

### 3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
dimethyl ether	01-2119472128-37	115-10-6	204-065-8	30-60	Flam. Gas 1, Press. Gas	H220,H280	A
4-methylpentan-2-one; isobutyl methyl ketone	01-2119473980-30	108-10-1	203-550-1	5-10	Flam. Liq. 2, Acute Tox. 4, Eye Irrit. 2, STOT SE 3	H225,H332,H319,H335	A
ethylbenzene	01-2119489370-35	100-41-4	202-849-4	1-5	Flam. Liq. 2, Acute Tox. 4, STOT RE 2, Asp. Tox. 1	H225,H332,H373,H304	A
1-methoxy-2-propanol; monopropylene glycol methyl ether	01-2119457435-35	107-98-2	203-539-1	1-5	Flam. Liq. 3, STOT SE 3	H226,H336	A
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime	01-2119539477-28	96-29-7	202-496-6	<1	Carc. 2, Acute Tox. 4, Eye Dam. 1, Skin Sens. 1	H351,H312,H318,H317	B
2-methoxy-1-methylethyl acetate	01-2119475791-29	108-65-6	203-603-9	0-1	Flam. Liq. 3	H226	A
Fatty acids, C6-19-branched, zinc salts	01-2119980048-32	68551-44-0	271-378-4	0-1	Aquatic Chronic 2	H411	
xylene	01-2119488216-32	1330-20-7	215-535-7	<12.5	Flam. Liq. 3, Acute Tox. 4, Acute Tox. 4, Skin Irrit. 2	H226,H332,H312,H315	A,W
trizinc bis(orthophosphate)	01-2119485044-40	7779-90-0	231-944-3	<2.5	Aquatic Acute 1, Aquatic Chronic 1	H400,H410	
zinc oxide	01-2119463881-32	1314-13-2	215-222-5	<0.25	Aquatic Acute 1, Aquatic Chronic 1	H400,H410	B

#### Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

W : Note: substance mentioned on the list of CMR-substances of the Dutch Ministry of Social Affairs and Employment (SZW)

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.



**Productname :** ZINC PRIMER  
**Ref.Nr.:** BDS000189\_3\_20200615 (EN)  
**Creationdate :** 15.06.20 Version : 2.3  
**Replaces:** BDS000189\_20181010

<b>Skin contact :</b>	Symptoms : sore throat, abdominal pain, nausea, vomiting Irritating to skin
<b>Eye contact :</b>	Symptoms : redness and pain Irritating to eyes Symptoms : redness and pain, impaired vision

#### 4.3. Indication of any immediate medical attention and special treatment needed

**General Advice :** If you feel unwell, seek medical advice (show the label where possible)  
If symptoms persist always call a doctor

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

foam, carbon dioxide or dry agent  
Do not use water jet extinguishing media, due to the risk of spreading fire.

#### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

#### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

#### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

#### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container  
This material and/or its container must be disposed of as hazardous waste.

#### 6.4. Reference to other sections



**Productname :** ZINC PRIMER  
**Ref.Nr.:** BDS000189\_3\_20200615 (EN)  
**Creationdate :** 15.06.20 Version : 2.3  
**Replaces:** BDS000189\_20181010

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
 Take precautionary measures against static discharges  
 Equipment should be earthed  
 Use explosion-proof electrical/ventilating/lighting/.../equipment.  
 Use only non-sparking tools.  
 Do not breathe aerosols or vapours.  
 Ensure adequate ventilation  
 Avoid contact with skin and eyes.  
 Wash thoroughly after use  
 Wear protective gloves/protective clothing/eye protection/face protection.  
 Eyewash bottles should be available

### 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
 Keep out of reach of children.

### 7.3. Specific end use(s)

Paints

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
ethylbenzene	100-41-4	TWA	100 ppm
		STEL	200 ppm
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	TWA	20 ppm
		STEL	50 ppm
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	1000 ppm
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm

**Productname :** ZINC PRIMER  
**Ref.Nr.:** BDS000189\_3\_20200615 (EN)  
**Creationdate :** 15.06.20 Version : 2.3  
**Replaces:** BDS000189\_20181010

National established exposure limits, United Kingdom			
ethylbenzene	100-41-4	TWA	100 ppm
		STEL	125 ppm
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	TWA	50 ppm
		STEL	100 ppm
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	400 ppm
		STEL	500 ppm
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
National established exposure limits, Ireland			
ethylbenzene	100-41-4	TWA	100 ppm
		STEL	200 ppm
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	TWA	20 ppm
		STEL	50 ppm
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	1000 ppm
		STEL	-
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime	96-29-7	TWA	3 ppm
		STEL	10 ppm

## 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation In all cases handle and use the product in accordance with good industrial hygiene practices.
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type AX)
<b>hands and skin :</b>	When handling the product wear chemical-resistant gloves (standard EN 374).
Recommended gloves:	Nitrile The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Depending on amount and duration of use and the risk of contact with the product the gloves manufacturer can assist you in the selection of the right glove material and breakthrough time.
<b>eyes :</b>	Wear safety eyewear according to EN 166.



<b>Productname :</b> ZINC PRIMER	<b>Creationdate :</b> 15.06.20	<b>Version :</b> 2.3
<b>Ref.Nr.:</b> BDS000189_3_20200615 (EN)	<b>Replaces:</b>	BDS000189_20181010

**Environmental protection:** Avoid release to the environment.  
Collect spillage.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Appearance : physical state :</b>	DME propelled liquid.
<b>colour :</b>	See color cap.
<b>odour :</b>	Characteristic odor.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	Not available.
<b>Flash point :</b>	15 °C (Closed Cup)
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	Not available.
<b>lower limit :</b>	Not available.
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	1.08 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Insoluble in water
<b>Auto-ignition :</b>	> 200 °C
<b>Viscosity :</b>	Not available.

### 9.2. Other information

<b>VOC = volatile organic compounds</b>	618 g/l
---	---------

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials



Productname : ZINC PRIMER  
 Ref.Nr.: BDS000189\_3\_20200615 (EN)  
 Creationdate : 15.06.20 Version : 2.3  
 Replaces: BDS000189\_20181010

Strong oxidising agent

## 10.6. Hazardous decomposition products

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

**acute toxicity:** based on available data the classification criteria are not met  
**skin corrosion/irritation:** Causes skin irritation.  
**serious eye damage/irritation:** Causes serious eye irritation.  
**respiratory or skin sensitisation:** based on available data the classification criteria are not met  
**germ cell mutagenicity:** based on available data the classification criteria are not met  
**carcinogenicity:** based on available data the classification criteria are not met  
**toxicity for reproduction:** based on available data the classification criteria are not met  
**STOT-single exposure:** based on available data the classification criteria are not met  
**STOT repeated exposure:** based on available data the classification criteria are not met  
**aspiration hazard:** based on available data the classification criteria are not met

### Information on likely routes of exposure:

**Inhalation :** Inhalation of solvent vapours may give rise to nausea, headaches and dizziness  
**Ingestion :** After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.  
**Skin contact :** Irritating to skin  
**Eye contact :** Irritating to eyes

### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LD50 oral rat	4016 mg/kg
		LC50 inhal.rat	27596 mg/l
		LD50 derm.rabit	2000 mg/kg
4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	LD50 oral rat	2080 mg/kg
		LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	10.8 mg/l
		LD50 derm.rat	> 5000 mg/kg
		LD50 derm.rabit	> 5000 mg/kg
dimethyl ether	115-10-6	LC50 inhal.rat	309 mg/l
zinc oxide	1314-13-2	LD50 oral rat	7950 mg/kg
		LC50 inhal.rat	> 5.7 mg/l
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime	96-29-7	LD50 oral rat	2326 mg/kg
		LD50 derm.rabit	1000 mg/kg





**Productname :** ZINC PRIMER  
**Ref.Nr.:** BDS000189\_3\_20200615 (EN)

**Creationdate :** 15.06.20 Version : 2.3  
**Replaces:** BDS000189\_20181010

## SECTION 12: Ecological information

### 12.1. Toxicity

Hazardous to the aquatic environment, chronic category 3  
 Harmful to aquatic life with long lasting effects.

#### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LC50 fish	6812 mg/l
		EC50 daphnia	23300 mg/l
4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	LC50 fish	505 mg/l
		2-methoxy-1-methylethyl acetate	108-65-6
dimethyl ether	115-10-6	LC50 fish	100-180 mg/l
		EC50 daphnia	> 400 mg/l
zinc oxide	1314-13-2	IC50 algae	154.9 mg/l
		LC50 fish	4.1 mg/l
		EC50 daphnia	4.4 mg/l
2-butanone oxime; ethyl methyl ketoxime; ethyl methyl ketone oxime	96-29-7	IC50 algae	0.136 mg/l
		LC50 fish	0.169 mg/l
		EC50 daphnia	1.7 mg/l
		LC50 fish	11.8 mg/l
		EC50 daphnia	> 100 mg/l
		EC50 daphnia	201 mg/l

### 12.2. Persistence and degradability

No experimental data available

### 12.3. Bioaccumulative potential

No experimental data available

### 12.4. Mobility in soil

Insoluble in water

### 12.5. Results of PBT and vPvB assessment

No information available

### 12.6. Other adverse effects

No experimental data available  
 GWP (global warming potential): 1

Productname : ZINC PRIMER  
Ref.Nr.: BDS000189\_3\_20200615 (EN)

Creationdate : 15.06.20 Version : 2.3  
Replaces: BDS000189\_20181010

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

National regulations : Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950

### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

### 14.4. Packing group

Packing group: Not applicable.

### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture



**Productname :** ZINC PRIMER  
**Ref.Nr.:** BDS000189\_3\_20200615 (EN)  
**Creationdate :** 15.06.20 Version : 2.3  
**Replaces:** BDS000189\_20181010

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

## 15.2. Chemical safety assessment

No information available

## SECTION 16: Other information

\*Explanation hazard statements: H220 : Extremely flammable gas.  
H225 : Highly flammable liquid and vapour.  
H226 : Flammable liquid and vapour.  
H280 : Contains gas under pressure; may explode if heated.  
H304 : May be fatal if swallowed and enters airways.  
H312 : Harmful in contact with skin.  
H315 : Causes skin irritation.  
H317 : May cause an allergic skin reaction.  
H318 : Causes serious eye damage.  
H319 : Causes serious eye irritation.  
H332 : Harmful if inhaled.  
H335 : May cause respiratory irritation.  
H336 : May cause drowsiness or dizziness.  
H351 : Suspected of causing cancer .  
H373 : May cause damage to organs through prolonged or repeated exposure  
.  
H400 : Very toxic to aquatic life.  
H410 : Very toxic to aquatic life with long lasting effects.  
H411 : Toxic to aquatic life with long lasting effects.

acronyms and synonyms: TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistent bioaccumulative toxic  
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.