

Keysight 8471D

Coaxial RF Microwave Detectors

100 kHz to 2 GHz

Data Sheet



Introduction

Features and Description

- Zero bias
- Environmentally rugged
- BNC connector

The Keysight Technologies, Inc. 8471D detector is a planar doped barrier detector offering the characteristics of the Keysight 8474 line of PDB detectors in an economical package. It is available with an BNC RF connector and BNC video connector.

The detector is designed for use in RF and microwave instrumentation and systems applications as the detecting element in leveling loops, for power monitoring and for wideband video detection.




Figure 1. Typical transfer characteristics.




Figure 3. Typical output response with temperature (pin 2 20 dBm).




Figure 2. Typical tangential sensitivity.




Figure 4. Typical video impedance variation with temperature.




Figure 5. Typical square law deviation.

Specifications

Frequency range		100 kHz to 2 GHz
Frequency response		±0.2 dB 100 kHz to 1 GHz; ±0.4 dB 1 to 2 GHz
SWR		< 1.23 0.0001 to 1 GHz; < 1.46 1 to 2 GHz
Low level sensitivity		0.5 mV/μW
Max operating input		100 mW
Typical short-term max input		0.7 Watt
Noise		< 50 μV (μV peak-to-peak with CW power applied to produce 100 mV output, 400 kHz BW)
Output polarity	(STD)	Negative
	(103)	Positive
Option	(102) ¹	Optimal square law load option

Note: Above specifications are at 25° C and ² 20 dBm unless otherwise specified.

Environmental

Operating temperature	-20° to +85° C
Non-operating temperature	MIL-STD 883, Method 1010: (-55° to +85°)
Vibration	MIL-STD 883, Method 2007: (0.6"D.A 20 to 80 Hz and 20g, 80 to 2000 Hz)
Shock	MIL-STD 883, Method 2002.1: (500g, 0.5 ms)
Altitude	MIL-STD 883, Method (50,000 ft, 15,240 m)
Moisture resistance	MIL-STD 883, Method 1004.1 (25° to 40° C, 95% RH)
RFI	MIL-STD 461C (meets Part 7, degraded by 10 dB)




Figure 6. Equivalent circuit for 8471D with typical parameter values.

Typical values:

R_v (diode video impedance) _ 1.5 k $\frac{1}{2}$ ²

C_b (RF bypass capacitor) _ 6800 pF nominal

$$T_R \text{ (10 to 90\% risetime) } _ 2.2 \frac{(R_{LOAD})(R_v)}{R_{LOAD}+R_v} (C_b+C_{LOAD}) = \frac{0.35}{BW}$$

Keysight 8471D

- A 13.72 (0.54)
- B 63.4 (2.50)
- C 15.64 (0.62)

Connector BNC (m) input:
BNC (f) output

Net weight: 38.8 grams (1.37 oz.)





Figure 7. 8471D

1. Option 102 external square law load extends the square law region of the detector with deviation of +/- 0.5 dB from the ideal square law response.
2. At 25° C and PIN ² 20 dBm (see Figure 3)

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries: www.keysight.com/find/contactus (BP-9-7-17)



www.keysight.com/go/quality
 Keysight Technologies, Inc.
 DEKRA Certified ISO 9001:2015
 Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.



Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.

Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/8471D

