




zQSFP+/QSFP28

TE Internal #: 2-2170808-4

QSFP28/56, Cage Assembly, Signal, Operating Temperature Range -40 – 85 °C [-40 – 185 °F], Data Rate (Max) 28 Gb/s, 2 Ports

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages



Pluggable I/O Product Type: **Cage Assembly**

Sealable: **No**

Circuit Application: **Signal**

Operating Temperature Range: **-40 – 85 °C [-40 – 185 °F]**

Data Rate (Max): **28 Gb/s**

Features

Product Type Features

Cage Type	Ganged
Thermal Accessory Type Included	Heat Sink
Pluggable I/O Product Type	Cage Assembly
Sealable	No
Form Factor	QSFP28/56

Configuration Features

Number of Rear EONs per Port Column	0
Number of Ports	2
Port Matrix Configuration	1 x 2

Electrical Characteristics

Data Rate (Max)	28 Gb/s
-----------------	---------

Body Features

Heat Sink Style	Pin
Heat Sink Finish	Anodized Black



Heat Sink Height	4.2 mm[.165 in]
------------------	-----------------

Heat Sink Height Class	PCI
------------------------	-----

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Termination Post & Tail Length	2.05 mm[.081 in]
--------------------------------	------------------

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
----------------------------	-----------------------------

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Other

Included Lightpipe	Yes
--------------------	-----

EMI Containment Feature Type	Internal/External EMI Springs
------------------------------	-------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)
--	--



Candidate List Declared Against: JUNE 2025 (250)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-2215048-0
ASSY, SEATING TL, QSFP28, 1X2

TE Part # CAT-C11-Z8
QSFP28 to QSFP28 Cable Assembly:
26 AWG

TE Part # 1888810-2
EMI/Dust Cover,XFP And QSFP

TE Part # CAT-Q17-N49033
QSFP56-Two QSFP56 Cable
Assembly: 30 AWG

TE Part # CAT-C11-Q17
QSFP56 to QSFP56 Cable Assembly:
26 AWG

TE Part # 1551920-2
zQSFP+ connector assembly

TE Part # CAT-Q17-N490325
QSFP56 to QSFP56 Cable Assembly:
30 AWG

TE Part # CAT-C11-N49
QSFP28-Two QSFP28 Cable
Assembly: 30 AWG

TE Part # CAT-C11-N490333
QSFP28-Four SFP+ Cable Assembly:
30 AWG

TE Part # CAT-Q17-N490333
QSFP56-Four SFP56 Cable Assembly:
26 AWG

TE Part # CAT-C11-N490325
QSFP28-Four SFP+ Cable Assembly:
26 AWG

TE Part # CAT-C11-Z806726
QSFP28 to QSFP28 Cable Assembly:
30 AWG




TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly:
30 AWG

Also in the Series | zQSFP+/QSFP28



Pluggable I/O Cable Assemblies(78)




Pluggable IO Connectors & Cages(394)




QSFP, QSFP+ & zQSFP+(394)

Customers Also Bought



TE Part #316998-7
CHAMP.050 REC HDR ASS'Y FMS TY




TE Part #556881-3
RCPT ASY,VRT,AMPINRGY WTB,3POS



TE Part #1116504-2
MJ,10MM,8P,NO SHIELD,SN TAILS




TE Part #1367073-1
20 POS SMT CONN, SFP, 15AU




TE Part #1586040-6
6P VAL-U-LOK VRT HDR W/P V0



TE Part #2-1676966-9
SMW2 1R5 5%



TE Part #1744037-6
06P EC PWR.200 CL HDR ASSY VRT



TE Part #CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS



TE Part #5177985-2
0.8FH,R05H.5,060,08/Sn,TR,SC



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-2170808-4_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2170808-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2170808-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English